

Line Trimmer XGT®

UR014G

40Vmax, 0 – 4 000 / 5000 min⁻¹

Model UR014G is a cordless Line Trimmer powered by 40VMax XGT Li-Ion battery

This model is a cordless solution for engine line trimmers, having the following excellent features:
High output power equivalent to that of 35 cc class engine models. Newly added "High-torque mode".
Low noise level. Loop handle and narrow protector, designed exclusively for use with nylon cutting head.



Technical specifications

Voltage XGT	✓
Nominal Battery Voltage	40 V
Battery Chemistry (Ni-Cd / Ni-MH / Li-ion)	Li-ion
No load speed	4000 - 5000 min ⁻¹
Cutting width	450 mm
Spindle Thread	M10 x 1,25 LH
Handle Type	L
Sound Power Level (L _{WA})	91,3 dB(A)
Sound Pressure Level (L _{pA})	77,9 dB(A)
Noise Uncertainty (K Factor)	2,9 dB(A)
Tool weight with battery	5,5 - 6,7 kg
Product Dimensions (L x W x H):	1914 x 330 x 304 mm
Nylon line- Diameter	2,7 mm
Brushless Motor	✓

User benefits

- Active Feedback sensing Technology (AFT) stops the engine if the rotation suddenly stops
- Brushless maintenance-free and long-life motor
- Battery protection circuit protects against overloading, over-discharging and over-heating
- Reverse rotation mode for removing entangled grass and weeds or changing the direction in which the cut grass is flown.

Link to product - www.makita.uk.com



Related products

Other

User manual

Parts drawing