



**Part Number :** [1110401404](#)

**Product Description :** QSFP+-to-QSFP+ Cable Assembly, 30 AWG, 4.0m Length

**Series Number :** 111040

**Status :** Obsolete

**Product Category :** High-Speed I/O Cable Assemblies



---

## Documents & Resources

### Drawings

[1110401404\\_sd.pdf](#)

---

## Product Environment Compliance

### Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant per EU 2015/863

### Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

### Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

### Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

---

## Part Details

### General

Status	Obsolete
Category	High-Speed I/O Cable Assemblies
Series	111040
Description	QSFP+-to-QSFP+ Cable Assembly, 30 AWG, 4.0m Length
Assembly Configuration	Dual Ended Connectors
Connector to Connector	QSFP+-to-QSFP+
Product Name	QSFP Plus,QSFP+
UPC	883906967536

### Agency

UL	E72548
----	--------

### Electrical

Impedance	100Ω
-----------	------

### Physical

Cable Length	4.0m
Circuits (Loaded)	MSA
Gender	Plug
Lock to Mating Part	Yes
Net Weight	297.900/g
Packaging Type	Bag
Single Ended	No
Wire/Cable Type	Round
Wire Size (AWG)	30

---

## Mates With / Use With

**Mates with Part(s)**

Description	Part Number
iPass I/O Right-Angle Surface Mount Receptacles	<u>75586</u>

**Use with Part(s)**

Description	Part Number
QSFP+ Cage Assemblies, Light Pipes, and Heat Sinks	<u>74750</u>
QSFP+ 1x3 Ganged Cage Assemblies and Heat Sink Clips	<u>74768</u>
QSFP+ Ganged Cages and Light Pipe Assemblies	<u>74769</u>

---

This document was generated on Aug 06, 2025

Obsolète