

Technical data sheet

Article number:
924-00498

BLT6

Product Group	Twin Bootlace Ferrules
Product Family	Nylon Insulated Twin Bootlace Terminals
Material	Copper (CU), Polyamide 6.6 (PA66)
Colour	Green (GN)
Application Range	Low Voltage
Conductor Size (mm²)	6 mm ²
Diameter (D)	10 mm
Halogen-free	Yes
Length (L)	26 mm
Length (L2)	12 mm
Length (L3)	14 mm
Max Voltage	600 V
Operating Temperature	-30 °C to +105 °C
Package Content packed in	bag
REACH Reg. Art.33 does not contain SVHC	Yes
ROHS compliant	Yes
Ø (D2)	4.8 mm
Width (W)	6.9 mm

HF ✓

RoHS ✓