

## Datasheet

ENGLISH

# RS PRO Panel Mounting printer

Stock No: 178-5732



This RS Pro panel mount printer is compact fixed head thermal line panel printer with a very shallow behind-panel depth. The transparent front paper cover gives visual indication of paper roll level. It has an electrical rating of 5.0VDC to 8.5VDC and 2A. RS232 Interface.

This printer has a resolution of 8dpmm (203dpi) with 384 dots per line. The effective printing width is 48mm.

### Features and Benefits

Simple drop-in easy paper loading for operational efficiency.

Data input is RS-232 serial.

Self-test function

Compact dimensions; Height 80mm, width 75mm, depth 45mm

Paper width is 57.5mm (max)

High performance thermal printer mechanisms ensure fast, reliable printing.

Reliable long life expectancy with MCBF 5~15 x 10<sup>6</sup>.

Easily embedded into many devices.

### Applications

Receipt printing

Medical equipment

Taxi Meter

Industrial Instruments

Portable printers and terminals

Test and measurement instruments

Ticket printing.