

JX.T – 3/8" Torx Bit Sockets



Description:

- **HIGH PERFORMANCE** - Designed and manufactured for extremely high tightening forces
- **BIT PROFILE** - For Female drive Fasteners
- **NECK-DOWN DESIGN** - Facilitating the use in narrow spaces
- **Matte finish**

	Fastener Head Size A (mm)	Square Drive	Tip Diameter A (mm)	Length L (mm)	Weight (g)
JX.8T	T8	3/8"	2.5	46	31
JX.10T	T10	3/8"	2.72	46	34
JX.15T	T15	3/8"	3.26	46	34
JX.20T	T20	3/8"	3.84	46	34
JX.25T	T25	3/8"	4.40	46	34
JX.27T	T27	3/8"	4.96	46	34
JX.30T	T30	3/8"	5.49	46	34
JX.40T	T40	3/8"	6.6	52.5	45
JX.45T	T45	3/8"	7.77	52.5	50
JX.50T	T50	3/8"	8.79	52.5	56
JX.55T	T55	3/8"	11.17	52.5	61