

Datasheet

## RS Pro 50 W Electronic Lighting Ballast, 220 to 240 V

RS Stock No: **796-1902**



### Product Details

RS Pro 50 W electronic lighting ballast works with voltages ranging from 220 - 240 V. This dimmable electronic driver can power both voltage LED strips and power current LEDs. It delivers high power, with active PFC and flexible selection of the output current.

### Features and Benefits

- Multi-power driver supplied with dip-switch for the selection of the output current
- Active power factor corrector
- Protections against overheating, short circuits, mains voltage spikes and overloads
- Can be switched on and off on secondary circuit for power LED

**Specifications:**

Ballast Type	Electronic
Dimensions	124 x 79 x 22 mm
Dimmable	Yes
Dimming Protocol	DALI, DMX
Frequency	50 to 60 Hz
Height	22 mm
Length	124 mm
Standards Met	EN 50172 (VDE 0108); EN 55015; EN 61000-3-2; EN 61000-3-3; EN 61347-1; EN 61347-2-13; EN 61547; EN 62384
Voltage Rating	220 to 240 V
Wattage	50 W
Width	79 mm