



Oil



Light Duty

Nitrile-coated work gloves with excellent grip, offering a more durable alternative to cotton

- **Assured protection:** ActivArm® 47-200 lightweight nitrile-coated gloves provide greater abrasion resistance* and hand protection against snags, punctures and cuts than standard 8oz/227g cotton or string-knit alternatives
- **Elevated comfort:** These ActivArm® gloves boast a flexible ergonomic design, with grip-enhancing nitrile coating on the fingers and palm, leaving the back of the hand with a cooler, more breathable feel
- **Food handling compliance:** Perfect for handling greasy or oily foodstuffs, ActivArm® 47-200 protective gloves satisfy relevant FDA food handling requirements

**they last 5x longer than standard cotton alternatives*



Industries

- Automotive
- Automotive Aftermarket
- Machinery and Equipment
- Metal fabrication
- Chemical

Applications

- Assembly & inspection of components
- Adjusting parts, systems
- Engine transmission and repair
- Assembling and mounting components
- Delivery of parts to production line
- Delivery of finished equipment
- Warehousing of raw materials
- Loading and unloading trucks and vehicles
- Loading and unloading of process equipment

Previously known as: Easy Flex® 47-200

Key Features

- **Lightweight nitrile coating:** Snag, puncture, cut and abrasion resistance
- **Flexible ergonomic design:** For comfortable safety gloves with a cool feel
- **FDA food handling compliance:** Assured food hygiene and hand protection

Performance Standards & Regulatory Compliance

ANSI/ISEA 105-2024



EN388: 2016



2111A

Specifications

BRAND STYLE	DESCRIPTION	Gauge	SIZE	LENGTH	COATING COLOR	PACKAGE
ActivArm® 47-200	Finishing: ¾ Coated Coating Material: Nitrile Liner Material: Interlock cotton Cuff Style: Knitwrist	N/A	6, 7, 8, 9, 10	272-289 mm; 10.70-11.37 inches	Green	12 pairs/bag, 12 bags/carton

For additional information visit us at www.ansell.com, or call us at

Europe, Middle East & Africa Region

Ansell Healthcare Europe NV
Riverside Business Park
Blvd International, 55
1070 Brussels, Belgium
T: +32 (0) 2 528 74 00
F: +32 (0) 2 528 74 01

Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.
Blvd. Bernardo Quintana No. 7001-C,
Q7001 Torre II,
Suites 1304, 1305 y 1306,
Col. Centro Sur, c.p. 76079
Queretaro, Qro. Mexico
T: +52 442 248 1544 / 248 3133

North America Region

Ansell Healthcare Products LLC
111 Wood Avenue South,
Suite 900
Iselin, NJ 08830, USA
T: +1 800 800 0444
F: +1 800 800 0445

Canada

Ansell Canada
105 Lauder
Cowansville, QC J2K 2K8
Canada
T: +1 800 363 8340
F: +1 800 267 3551

Australia

Ansell Limited
Level 3, 678 Victoria Street,
Richmond, Vic, 3121
Australia
T: +61 1800 337 041
F: +61 1800 803 578

Asia Pacific Region

Ansell Global Trading Center
(Malaysia) Sdn Bhd
Prima 6, Prima Avenue
Block 3512, Jalan Teknokrat 6
T: +603 8310 6688
F: +603 8310 6699