

Features

- Intrinsically safe for use in hazardous locations
- Switchable high and low light output
- High power CREE LED
- IP67 Waterproof rated
- Tough and durable casing
- Screw fastened battery compartment

RS PRO ATEX LED Head Torch 200 lm, 100 m Range

RS Stock No.: 0145619



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

Product Description

RS PRO ATEX Head Torch

Introducing the RS PRO ATEX Head Torch, the perfect companion in hazardous environments. Boasting a high-powered CREE LED, this head torch delivers exceptional performance even in the toughest conditions, while the formidable 200 lumens output, and impressive 100-meter beam distances ensures optimal visibility. Experience uninterrupted lighting for up to 2.5 hours, with a toggle option of high and low light modes for additional versatility extends the runtime to a maximum of 4.5 hours. Trust in a robust design and cutting-edge features to give confidence in a range of applications thanks to this RS PRO head torch.

Features and Benefits:

- This RS PRO Head Torch is ATEX protected and specifically engineered for use in hazardous environments, providing peace of mind in challenging conditions
- Easily toggle between high and low light settings with a convenient single button at the top of the torch, allowing the user to adapt to varying lighting needs
- The cutting-edge CREE LED technology ensures a superior lighting experience with an incredible 200 lumens output and 100 meter beam distance for optimum performance and usage, especially in challenging environment
- Designed for rugged durability, the casing protects against impacts and drops up to 1 meter, while the IP67 rating offers increased protection when the head torch is being used in the elements, ensuring optimum performance and reliability in diverse weather conditions
- The vibrant yellow colour and black adjustable elasticated head strap offer visibility and enhanced comfort during use, especially when the head torch is being worn for extended periods of time
- Equipped with a built-in gas release vent for enhanced safety during use and a screw-fastened battery compartment to add an extra layer of security, this head torch is the perfect addition for anyone requiring a superior hands-free lighting experience in a range of environments

General Specifications

Torch Style	Head Torch
Lamp Type	LED
Luminosity	200lm (high)/ 100lm (low)
Range	100m
Beam Type	Flood
Switching Modes	Hight/Low/Off
Light Colour	white
Case Material	Anti static plastic
Anti-Corrosive	Yes
Drop Resistance	1m
Zone	Zone 0
Hazardous Area	Yes

Modes Specifications

Parameters	High Mode	Low Mode / Strobe
Light Output	216lm	100m
Run Time	5 hours	12.2 hours
Beam Distance	100m	75m

Electrical Specifications

Rechargeable	No
Batteries	3 x AAA alkaline battery
Battery Indicator	No
Switch Type	Button switch






Mechanical Specifications

Length	80mm
Width	50m
Depth	45mm
Weight (with Batteries)	130

Protection Category

IP Rating	IP67
-----------	------

Approvals

Compliance/Certifications	CE / UL / ATEX / IECE /
Standards Met	<div>  <p>Class I Div 1&2 Grp ABCD / Class II Div 1&2 Grp EFG Class III / Temperature Code T4 IP67 File number: E324236</p> </div> <div>  <p>II 1G Ex ia IIC T4 Ga IP67 UL 22 ATEX 2757X UL 22 UKEX 2594X</p> </div> <div>  <p>Ex ia IIC T4 Ga IP67 IECEX UL 22.0035X</p> </div> <div>  <p>0518</p> </div> <div>  <p>2813</p> </div>
Hazardous Area Certification	ATEX; IECEX

Similar Products

Stock No.	Brand	Product Name	Luminosity	Batteries	Colour
0145616	RS PRO	ATEX Torch	180 lm (high)/ 70lm (low)	4 x AA	Yellow
0145619	RS PRO	ATEX Head Torch	200lm (high)/ 100lm (low)	3 x AAA	Yellow
0145618	RS PRO	ATEX Torch	133lm (high)/ 32lm (low)	4 x AA	Yellow