



Part No. 112100455

Series MultiFLOW air and fluid gun

3D

PDF

Inquiry List

Class title
Adjustable jet
Connection
G 1/2" (fem)
Standards
OSHA STD 01-13-001
Material
POM, TPE, aluminum, steel
Media
Air and non-explosive water based liquids
Material seal
NBR (Nitrile)
Max working pressure (bar)
16 bar (232 PSI)

Min. burst pressure (bar)

64 bar (928 PSI)

MultiFLOW air and fluid gun

CEJN's MultiFLOW blow gun effectively cleans surfaces with air or water with unparalleled blowing force. Precise flow is achieved by adjustable flow settings. Nozzle adjusts from narrow jet to wide beam. The MultiFLOW meets and exceeds OSHA safety standards when dead-ended.



Check with an authorized CEJN distributor for availability and prices. All measurements are in mm. Other connections and sealing material on request. Some part numbers may be subject to minimum order quantities. CEJN reserves the right to make changes without further notification. Thread connections are listed according to ISO standards, unless stated otherwise.