

Sep.1.2018 Copyright 2018 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
 In case that the application demands a high level of reliability, such as automotive,
 please contact a company representative for further information.

APPLICABLE STANDARD				
RATING	OPERATING TEMPERATURE RANGE	1 -25 °C TO +105 °C	STORAGE TEMPERATURE RANGE	-10 °C TO +60 °C
	VOLTAGE	_____	APPLICABLE CABLE	14 mm ² or AWG #6 OUTER DIAMETER: φ12.4 max.
	CURRENT	2 70A		

SPECIFICATIONS

ITEM	TEST METHOD	REQUIREMENTS	QT	AT
------	-------------	--------------	----	----

CONSTRUCTION


GENERAL EXAMINATION	VISUALLY AND BY MEASURING INSTRUMENT.	ACCORDING TO DRAWING.	X	X
---------------------	---------------------------------------	-----------------------	---	---

COUNT	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE
△				

REMARK NOTE 1 OPERATING TEMPERATURE RANGE INCLUDES THE TEMPERATURE RISE BY CURRENT CARRYING. 2 RATING CURRENT SHALL BE TESTED UNDER MATED CONDITION WITH AN APPLICABLE CONNECTOR.	APPROVED	SU. OBARA	13.02.22
	CHECKED	YH. YAMADA	13.02.22
	DESIGNED	HS. KAWASHIMA	13.02.22
	DRAWN	KN. IKEHARA	13.02.22

Unless otherwise specified, refer to JIS C 5402, IEC 60512.

Note QT:Qualification Test AT:Assurance Test X:Applicable Test	DRAWING NO.	ELC4-118155-00
--	-------------	----------------

	SPECIFICATION SHEET	PART NO.	EF1-38-14	
	HIROSE ELECTRIC CO., LTD.	CODE NO.	CL142-0008-2-00	△ 1/1