

Cable lug - C-BCI 6/2,8 - 3240047

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)

Flat pin cable lug, yellow, 4 - 6 mm²,




Why buy this product

- 'EASY ENTRY' for easy and reliable conductor entry
- Halogen-free
- Electrolytic tin plating



Key commercial data

Packing unit	50 pc
Minimum order quantity	100 pc
GTIN	 4 046356 452656
Weight per Piece (excluding packing)	1.74 g
Custom tariff number	85366990
Country of origin	China

Technical data

Dimensions

Length (b)	32 mm
Width (a)	2.8 mm
Length contact range	18 mm
Length of insulation sleeve (c)	14 mm
Inner dimension of the insulating collar (d)	6.5 mm
Material thickness (g)	0.8 mm

Ambient conditions

Ambient temperature (operation)	-20 °C ... 105 °C
Short-term temperature	120 °C
Max. permanent temperature	105 °C

General

Cable lug - C-BCI 6/2,8 - 3240047

Technical data

General

Color	yellow
Stripping length	9 mm
Components	Halogen-free
Inflammability class according to UL 94	V2
Material	Copper

Classifications

eCl@ss

eCl@ss 4.0	27060701
eCl@ss 4.1	27060701
eCl@ss 5.0	27400201
eCl@ss 5.1	27400204
eCl@ss 6.0	27400204
eCl@ss 7.0	27400204
eCl@ss 8.0	27400204

ETIM

ETIM 2.0	EC000005
ETIM 3.0	EC000005
ETIM 4.0	EC001052
ETIM 5.0	EC001052

UNSPSC

UNSPSC 6.01	30212109
UNSPSC 7.0901	27121703
UNSPSC 11	27121703
UNSPSC 12.01	27121703
UNSPSC 13.2	27121703

Drawings

Dimensioned drawing

