Stapler LXT®

DST221

18V • 10 mm • 10 – 22 mm

Suitable for quick and easy fixing of MDF roofing panels and other construction materials

An 18V battery-operated stapler for quick and easy fixing of construction plastics and other materials. Ideal for fixing of MDF roofing panels. Approx. 3 000 staples per battery charge.



LXT

Technical specifications

Voltage LXT	✓
Staple Crown Width	10 mm
Staple range	10 - 22 mm
Staple Wire Section	0,6 x 1,2 mm
Fastener Magazine Capacity	98
Nominal Battery Voltage	18 V
Sound Pressure Level (L_{pA})	82 dB(A)
Noise Uncertainty (K Factor)	3 dB(A)
Vibration Level (3 axes)	3,5 m/s²
Vibration Uncertainty (K Factor)	1,5 m/s²
Tool weight with battery	2,4 kg
Product Dimensions (L x W x H):	251 x 91 x 212 mm
Staple measures	10 x 10 - 22 mm
Fastener Gauge	0,6 x 1,2 Ga
Depth Adjustment	✓

User benefits

- Soft grip handle provides increased comfort on the job
- Depth adjustment
- The rubber coating on the handle ensures a firm working grip
- Fast and effortless fastening of building plastics and materials.
- Battery protection system automatically shuts off power when the battery level is low

Link to product - www.makitauk.com

Related products

Optional AC

821550-0
Makpac case (2)



837640-9
MakPac (2) Inlay



Other

User manual

Parts drawing