



IR HL450

INTERNAL USB RECHARGEABLE HEADLAMP 450 LUMENS

- 450 lumens of TRUEVIEW™ high definition output with up to 100 m beam distance
- Flood, Spot and Spot/ Flood beam options in different output modes for optimal brightness and up to 16 hrs run time
- 4 mounting clips for securing to helmets and adjustable strap with rubber grip
- Detachable magnetic light head attachment for hands-free use and storage
- IP54 rating, light is protected from dust and falling water
- Conveniently charge MILWAUKEE® RECHARGEABLE internal battery with micro-USB cable from USB power source or AC outlet (wall plug not included)
- Fuel gauge allows fast checking of battery charge
- Jobsite tough micro-USB braided cable with metal ends
- Includes USB cable



Max. light output hybrid mode / spot low / spot high / flood low / flood high (lumens)	450/ 100/ 250/ 50/ 250
Max. run time (h)	2.5/ 8/ 4/ 14/ 4
Weight with battery pack (EPTA) (kg)	0.12 (w/ internal battery)
Kit included	Integrated battery, USB cable, Blister packaging
Article Number	4933478587