



# FLIR DM92/ DM93

## True RMS Industrial Multimeters

FLIR's latest choice of new world-class digital multimeters offer advanced variable frequency drive filtering to help you accurately analyze non-traditional sine waves and noisy signals.

- LoZ Mode eliminates ghost voltage error readings caused by long wires that share a conduit
- Powerful LED worklights eliminate the need for a flashlight while performing tests in dim lighting
- Manually store and recall up to 99 readings
- Durable double molded construction (IP54, 2m Drop Test)

## KEY FEATURES

- TRMS Voltage and Current, Bright White LED Backlight, Analog Bargraph, Auto AC/DC Voltage, Min, Max, Average Recording, Auto Power Off, Data Hold, Relative, Peak Hold

## DM93 ADDITIONAL FEATURES

- Data Record captures electrical measurements and provides wireless data transfer
- Integrated Bluetooth® technology connects the FLIR DM93 to the FLIR Tools Mobile app on compatible mobile device for remote viewing and sharing
- METERLiNK® technology wirelessly sends the meter's electrical readings to compatible FLIR infrared cameras, embedding the data into live and saved thermal images

## INCLUDES

- CAT IV Silicone Test Leads, 6 AAA Batteries, User Manual/CD, and Limited Lifetime Warranty.
- Model DM93 also includes a Type K Temperature Probe (400°F, 204°C) and Magnetic Hanging Strap



## Specifications

TECHNICAL SUMMARY	MAX RANGE	BASIC ACCURACY
DC Voltage	1000.0V	±0.05%
AC Voltage	1000.0V	±0.5%
VFD AC Voltage	1000.0V	±0.5%
DC Current	10.000A	±0.2%
AC Current	10.000A	±1.0%
Resistance	40.00MΩ	±0.2%
Continuity Threshold	30Ω	±0.2%
Frequency	100.00kHz	±5 Digits
Capacitance	40.00mF	±0.9%
Temperature	-328 to 2192°F, -200 to 1200°C	±1.0%
Diode Test	2V	±1.5%
GENERAL INFORMATION		
Display Counts	40,000	
IP Rating, Drop Test	IP 54, 2m (6.6')	
Category Rating	CAT IV-600V, CAT III-1000V	
Battery Type	6 x AAA	
Bluetooth Range Max (DM93 only)	32ft (10m)	
Data Recording (DM93 only)	20,000 Pts (125 days max)	
Memory	99 internal storage locations	
Warranty	Limited Lifetime*	

\* When registered within 60 days of purchase.



DM92 Features powerful worklights

## Ordering Information

DM92 ..... True RMS Industrial Multimeter with VFD Mode  
 DM92-NIST ..... DM92 with Certificate of Traceability to NIST  
 DM93 ..... True RMS Industrial Multimeter with VFD Mode and Bluetooth  
 DM93-NIST ..... DM93 with Certificate of Traceability to NIST

## Accessories

TA10 ..... Protective case for DM9x and IM7x Series  
 TA50 ..... Magnetic Hanging Strap  
 TA60 ..... Thermocouple adapter and Type K probe  
 TA70 ..... CAT IV Insulated Alligator Clips  
 TA80 ..... CAT IV Silicone Test Leads



### BOSTON

FLIR Systems, Inc.  
 9 Townsend West  
 Nashua, NH 03663  
 USA  
 PH: +1 266.477.3687

### PORTLAND

Corporate Headquarters  
 FLIR Systems, Inc.  
 27700 SW Parkway Ave.  
 Wilsonville, OR 97070  
 USA  
 PH: +1 866.477.3687

### NETHERLANDS

FLIR Systems, Ltd.  
 Charles Petitweg 21  
 4847 NW Breda  
 Netherlands  
 PH: +31 (0) 765.41.85

### CHINA - BEIJING

Room 502, West Wing,  
 Hanwei Building  
 No. 7 Guanghua Avenue  
 Chaoyang District,  
 Beijing 100004,  
 China  
 PH: +010.59797755

www.flir.com  
 NASDAQ: FLIR

Equipment described herein may require US Government authorization for export purposes. Diversion contrary to US law is prohibited. Imagery for illustration purposes only. Specifications are subject to change without notice. ©2014 FLIR Systems, Inc. All rights reserved. (Created 09/14)