



Datasheet

Stock No: 684-349

ENGLISH

RS Pro Copper Bar, 1000mm x 20mm x 6mm



Product Details:

Copper HDHC Rod, Bar & Sheet

A high conductivity, corrosion resistant, malleable copper in rod, bar and sheet form.

Chemical analysis:	
Copper	99.90
Lead	0.005
Bismuth	0.001
Tensile Strength:	
Sheet	240N/mm ²
Half Hard	240N/mm ²

Standards

BS2874/C101 (1986), BS EN 12164 CW 004A

Specifications:

Material:	Copper
Form:	Rectangular Bar
Length:	1000mm
Width:	20mm
Height:	6mm
Tensile Strength:	240 N/mm ²