



M18 FUEL 38mm Magnetic Drill

M18 FMDP-0C0

- POWERSTATE Brushless Motor: Delivers maximum power and longer motor life.
- REDLINK PLUS Intelligence prevents damage to the tool and battery due to overloading or overheating
- REDLITHIUM-ION Batteries deliver more work per charge and more work over the life of the battery

MODEL VARIANT



INCLUDES

- M18 FMDP-0C0 (1)

Categories: Drilling

WHERE TO BUY

PRODUCT SPECIFICATIONS

Battery platform	M18 REDLITHIUM-ION
Voltage (V)	18
FUEL Gauge	Yes
LED Light	Yes
No Load Speed (rpm)	400 / 690
Chuck Size (mm)	13
Stroke Length (mm)	146
Tool Reception	Weldon
Max. holding power (at drill point pressure) (N)	8890
Max. depth broaching capacity (mm)	50
Max. diameter broaching capacity (mm)	38
Max. drilling solid bit (mm)	13
Weight with battery pack if applicable (kg)	13.7kg (5.0Ah)

