

# MB4/6.L2

ABB contact for United Kingdom



## General Information

<b>Extended Product Type:</b>	MB4/6.L2
<b>Product ID:</b>	1SNA115406R1300
<b>EAN:</b>	3472591154061
<b>Catalog Description:</b>	MB4/6.L2 Distribution Terminal Blocks
<b>Long Description:</b>	MB4/6.L2 Distribution Terminal Blocks - Grey,4mm <sup>2</sup> RatedCrossSection, 14.5mm Spacing G32, TH 35-7.5, TH 35-15 Rail

## Categories

Products » Low Voltage Products and Systems » Connection Devices » Terminal Blocks » Distribution Terminal Blocks

## Ordering

<b>EAN:</b>	3472591154061
<b>Minimum Order Quantity:</b>	25 piece
<b>Customs Tariff Number:</b>	85369010

## Dimensions

<b>Product Net Width:</b>	14.5 mm
<b>Product Net Height:</b>	44.5 mm
<b>Product Net Depth:</b>	40.5 mm
<b>Product Net Weight:</b>	19 g

## Container Information

<b>Package Level 1 Units:</b>	25 piece
<b>Package Level 1 Width:</b>	81 mm
<b>Package Level 1 Height:</b>	47 mm
<b>Package Level 1 Length:</b>	220 mm
<b>Package Level 1 Gross Weight:</b>	0.475 kg
<b>Package Level 1 EAN:</b>	3472591154061
<b>Package Level 2 Units:</b>	350 piece
<b>Package Level 2 Width:</b>	300 mm
<b>Package Level 2 Height:</b>	150 mm
<b>Package Level 2 Length:</b>	500 mm
<b>Package Level 2 Gross Weight:</b>	7.07 kg
<b>Package Level 3 Units:</b>	16800 piece
<b>Product Packing Type:</b>	Box

## Environmental

<b>RoHS Status:</b>	Following EU Directive 2002/95/EC August 18, 2005 and amendment
---------------------	---

## Technical UL/CSA

ABB's website uses cookies. By staying here you are agreeing to our use of cookies. [Learn more](#)

<b>Connection Type:</b>	Screw clamp
<b>Function:</b>	Distribution
<b>Gauge(s) of Form:</b>	A4

<b>IIT Publishing Status:</b>	Level 0 - Information enabled
<b>Mounting on DIN Rail:</b>	G32 (32 x 15 mm Mounting Rail) acc. to IEC 60715 TH35-7.5 (35 x 7.5 mm Mounting Rail) acc. to IEC 60715 TH35-15 (35 x 15 mm Mounting Rail) acc. to IEC 60715
<b>Number of Levels:</b>	1
<b>Pollution Degree:</b>	2
<b>Product Main Type:</b>	MB4/6
<b>Product Name:</b>	Terminal Block
<b>Rated Cross-Section:</b>	4 mm <sup>2</sup>
<b>Rated Impulse Withstand Voltage (U<sub>imp</sub>):</b>	8 kV
<b>Recommended Screw Driver:</b>	4 mm
<b>Spacing:</b>	6 mm
<b>Sub-Function:</b>	Phases
<b>Wire Stripping Length:</b>	9.5 mm

### Certificates and Declarations (Document Number)

<b>Declaration of Conformity - CE:</b>	1SND225024C1005
<b>EAC Certificate:</b>	1SND161009A1100
<b>RoHS Information:</b>	1SND230023F0202

### Classifications

<b>ETIM 4.0:</b>	EC001894 - Distributor assembly terminal blocks
<b>ETIM 5.0:</b>	EC001894 - Distributor assembly terminal blocks
<b>Object Classification Code:</b>	X

