


## FEATURES

- **IP66 Rating:** Provides excellent protection against dust and water, suitable for outdoor environments.
- **Constant Voltage Operation:** Ensures stable power supply to LED systems, enhancing performance and longevity.
- **Wide Input Voltage Range:** Operates efficiently between 200 and 240 V AC, accommodating various power sources.
- **High Output Power:** Delivers up to 150W, supporting large-scale lighting installations.
- **Multiple Dimming Options:** Compatible with Leading Edge, PWM, and Trailing Edge dimming for flexible lighting control.
- **Single Output:** Simplifies installation and reduces wiring complexity.

## RS PRO 150W LED Driver, 24V Constant Voltage

RS Stock No: 642-793



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

### Product Description

The RS PRO 150W LED Driver is designed to provide reliable power to LED lighting systems. With a constant voltage output of 24V, it ensures stable and efficient operation for a variety of lighting applications. Its robust design and IP66 rating make it suitable for both indoor and outdoor use, offering protection against dust and water ingress.

### General Specifications

Dimming Operation	Leading Edge, PWM, Trailing Edge
Number of Outputs	1
Operating Modes	Constant Voltage
Primary Type	AC
Product Type	LED Driver
Sub Type	Constant Voltage LED Driver

### Electrical Specifications

Driver Current	6.25 A
Input Voltage	200-240 V ac
Input Voltage Type	AC
Maximum Output Power	150 W
Output Voltage	24 V

### Protection Category

IP Rating	IP66
-----------	------

### Approvals

Standards/Approvals	CE, EN55015, EN61000-3-2, 3, EN61000-4-2,3,4,5,6,11, EN61347-1, EN61347-2-13, EN61547
---------------------	---