

1470-19 (3/11)

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

SEP, 2005.

© COPYRIGHT 2005 By -

ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

変更

DESCRIPTION

DATE

DWN

APVD

P



LTR

SEE SHEET 1




-

-

-



PANEL CUT OUT DIMENSION (REFERENCE)

P.C.B LAYOUT (REFERENCE)
SHOWN AS CONNECTOR MOUNTING SIDE
TOLERANCE: NON-CUMULATIVE

BRASS	CONTACT	(3)
PHOSPHOR BRONZE	SHELL	(2)
GLASS FILLED LCP UL94V-0, BLACK COLOR	HOUSING	(1)
MATERIAL	DESCRIPTION	ITEM

CONNECTOR: WITHOUT FLANGE THROUGH HOLE TYPE

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
単位: 英
mmTOLERANCES UNLESS
OTHERWISE SPECIFIED:
一般公差0 PLC
1 PLC
2 PLC
3 PLC
4 PLC
ANGLES
FINISH
仕上MATERIAL
材料

DWN

CHK

APVD

PRODUCT SPEC
製品規格APPLICATION SPEC
取付適用規格

WEIGHT

CUSTOMER DRAWING

TE

TE Connectivity

HDMI 19 POS RECEPTACLE ASSY
SMT SHORT TYPE

SIZE

CAGE CODE

DRAWING NO
番号

A300779

C=1903015

RESTRICTED TO

SCALE
尺度 4:1



SHEET

2 OF 12




REV

R

LOC	DIST	REVISIONS					
		変更					
—	—	P	LTR	DESCRIPTION	DATE	DWN	APV
			—	SEE SHEET 1	—	—	—



PANEL CUT OUT DIMENSION (REFERENCE)



P.C.B LAYOUT (REFERENCE)
SHOWN AS CONNECTOR MOUNTING SIDE
TOLERANCE: NON-CUMULATIVE

POLYIMIDE	TAPE	④
BRASS	CONTACT	③
PHOSPHOR BRONZE	SHELL	②
GLASS FILLED LCP UL94V-0, BLACK COLOR	HOUSING	①
MATERIAL	DESCRIPTION	ITEM

CONNECTOR: WITH FLANGE THROUGH HOLE TYPE

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN		 TE Connectivity			
		CHK					
DIMENSIONS: 單位: 英 mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: 一般公差		NAME 名稱		HDMI 19 POS RECEPTACLE ASSY SMT SHORT TYPE	
		0 PLC ±		APVD			
		1 PLC ±		PRODUCT SPEC 製品規格			
		2 PLC ±		APPLICATION SPEC 取付適用規格			
		3 PLC ±		SIZE		CAGE CODE	
		4 PLC ±		DRAWING NO 番号		RESTRICTED	
ANGLES ±				A3		00779	
FINISH 仕上		WEIGHT		C=1903015		—	
MATERIAL 材料		CUSTOMER DRAWING				SCALE 原尺	
						4:1	
						SHEET	
						3 OF 12	
						REV	

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

SEP, 2005.

© COPYRIGHT 2005 By -

ALL RIGHTS RESERVED.

LOC
—
DIST
—

REVISIONS



変更

DESCRIPTION


DATE

DWN



APVD

P LTR
— SEE SHEET 1


PANEL CUT OUT DIMENSION (REFERENCE)



P.C.B LAYOUT (REFERENCE)
SHOWN AS CONNECTOR MOUNTING SIDE
TOLERANCE: NON-CUMULATIVE



CONNECTOR: WITH FLANGE THROUGH HOLE TYPE



POLYIMIDE	TAPE	(4)
BRASS	CONTACT	(3)
PHOSPHOR BRONZE	SHELL	(2)
GLASS FILLED LCP UL94V-0, BLACK COLOR	HOUSING	(1)
MATERIAL	DESCRIPTION	ITEM

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
単位: 英
mmTOLERANCES UNLESS
OTHERWISE SPECIFIED:
一般公差

0 PLC ±
1 PLC ±
2 PLC ±
3 PLC ±
4 PLC ±
ANGLES ±
FINISH 仕上

MATERIAL
材料

DWN

CHK

APVD

PRODUCT SPEC
製品規格APPLICATION SPEC
取付適用規格

WEIGHT

CUSTOMER DRAWING

TE

TE Connectivity

HDMI 19 POS RECEPTACLE ASSY
SMT SHORT TYPE

SIZE

CAGE CODE

DRAWING NO
番号

A3

00779

C=1903015

RESTRICTED TO

SCALE
尺度


4:1

SHEET




4 OF 12

REV

R



PANEL CUT OUT DIMENSION (REFERENCE)



P.C.B LAYOUT (REFERENCE)
SHOWN AS CONNECTOR MOUNTING SIDE
TOLERANCE: NON-CUMULATIVE

BRASS	CONTACT	③
PHOSPHOR BRONZE	SHELL	②
GLASS FILLED LCP UL94V-0, BLACK COLOR	HOUSING	①
MATERIAL	DESCRIPTION	ITEM

CONNECTOR: WITH FLANGE FULL SMT TYPE

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN		 TE Connectivity			
		CHK					
DIMENSIONS: 單位: 吋 mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: 一般公差		NAME 名稱		HDMI 19 POS RECEPTACLE ASSY SMT SHORT TYPE	
		0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ±		APVD PRODUCT SPEC 製品規格			
MATERIAL 材料		FINISH 仕上		APPLICATION SPEC 取付適用規格		SIZE A3	
		WEIGHT		CAGE CODE 00779		DRAWING NO 番号 C=1903015	
CUSTOMER DRAWING				SCALE 尺度 4:1		SHEET 5 OF 12	
				REV R		RESTRICTED TO —	

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

SEP, 2005.



© COPYRIGHT 2005 By -

ALL RIGHTS RESERVED.


1903015-1, 2-1903015-2, 5-1903015-1

5-1903015-5, 7-1903015-1; AS SHOWN


LOC	DIST	REVISIONS			DATE	DWN	APVD
		P	LTR	DESCRIPTION			
		-	-	SEE SHEET 1	-	-	-

5-1903015-3; AS SHOWN
(SCALE 1:1)


DETAIL A




B-B

5-1903015-9; AS SHOWN
(SCALE 1:1)


DETAIL A




B-B

9-1903015-3; AS SHOWN
(SCALE 1:1)


DETAIL A



B-B



B-B



SEE DETAIL A

WEEDING THE COVER TAPE: 300 MIN
(NOT INCLUDE EMPTINESS POCKET)PEELING ANGLE: 165°~180°
PEELING STRENGTH:
0.1~0.7N (300mm/min.)

PLASTIC REEL


PULL OUT DIRECTION

CARRIER TAPE


LABEL

400 MIN. WITH PRODUCT CHARGE 25 HOLES MIN.
QTY: T PCS

LABEL DESCRIPTION

TYCO P/N: *-1903015-*
QTY: * pcs
D/C: MADE IN CHINA1903015-3; AS SHOWN
(SCALE 1:1)

DETAIL A



B-B

PET	COVER TAPE
PS	CARRIER TAPE
PLASTIC	REEL
MATERIAL	DESCRIPTION

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
單位: 毫米TOLERANCES UNLESS
OTHERWISE SPECIFIED:
一般公差0 PLC ±
1 PLC ±
2 PLC ±
3 PLC ±
4 PLC ±
ANGLES ±MATERIAL
材料FINISH
仕上

DWN

CHK

APVD

PRODUCT SPEC
製品規格APPLICATION SPEC
取付適用規格

WEIGHT

CUSTOMER DRAWING

TE

TE Connectivity

HDMI 19 POS RECEPTACLE ASSY
SMT SHORT TYPE

SIZE

CAGE CODE

DRAWING NO
番号

A3

00779

C=1903015

RESTRICTED TO

SCALE
尺度 4:1

SHEET

6 OF 12

REV
R

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION





SEP, 2005.

© COPYRIGHT 2005 By -

ALL RIGHTS RESERVED.

1903015-2, 1903015-5, 4-1903015-1, 5-1903015-2, 5-1903015-4
8-1903015-4, 9-1903015-4; AS SHOWN

LOC	DIST	REVISIONS			
		P	LTR	DATE	DWN
-	-	-	-	SEE SHEET 1	-



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN		CHK	
DIMENSIONS: 單位: 毫米 mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: 一般公差		APVD	
0 PLC ±		1 PLC ±		PRODUCT SPEC 製品規格	
2 PLC ±		3 PLC ±		APPLICATION SPEC 取付適用規格	
4 PLC ±		FINISH 仕上		WEIGHT	
MATERIAL 材料		CUSTOMER DRAWING		SCALE 尺度 4:1	
NAME 名称		SIZE A3		CAGE CODE 00779	
DRAWING NO 番号		DRAWING NO 番号		RESTRICTED TO	
HDMI 19 POS RECEPTACLE ASSY SMT SHORT TYPE		DRAWING NO 番号		SHEET 7 of 12	
REV R		REV R		REV R	

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

SEP ,2005.

© COPYRIGHT 2005 By --

ALL RIGHTS RESERVED.

1903015-4; AS SHOWN

LOC

DIST

REVISIONS

變更

DESCRIPTION

DATE

DWN

APVD

P




LTR

SEE SHEET 1


--

--

--



DETAIL C
(SCALE 2:1)



THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
單位: 毫米

TOLERANCES UNLESS
OTHERWISE SPECIFIED:
一般公差

- 0 PLC ±
- 1 PLC ±
- 2 PLC ±
- 3 PLC ±
- 4 PLC ±
- ANGLES ±
- FINISH 仕上

MATERIAL
材料

DWN

CHK

APVD

PRODUCT SPEC
製品規格

APPLICATION SPEC
取付適用規格

WEIGHT

CUSTOMER DRAWING



TE Connectivity

HDMI 19 POS RECEPTACLE ASSY
SMT SHORT TYPE

SIZE

CAGE CODE

DRAWING NO
番号

A3

00779

C=1903015

RESTRICTED TO




SCALE
尺度 4:1

SHEET
8 of 12


REV
R

1903015-7, 1903015-8; AS SHOWN


LOC	DIST	REVISIONS				DATE	DWN	APVD
		P	LTR	変更	DESCRIPTION			
-	-	-	-	SEE SHEET 1		-	-	-



DETAIL C
(SCALE 2:1)




THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN		CHK		APVD		NAME		HDMI 19 POS RECEPTACLE ASSY SMT SHORT TYPE		RESTRICTED TO	
DIMENSIONS: 単位: 話 mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: 一般公差		PRODUCT SPEC 製品規格		APPLICATION SPEC 取付適用規格		SIZE		CAGE CODE		DRAWING NO 番号	
MATERIAL 材料		FINISH 仕上		WEIGHT		CUSTOMER DRAWING		A3		00779		C=1903015	
								SCALE 尺度		SHEET 9 of 12		REV R	



TRAY B

TRAY B (EMPTY)



4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

SEP ,2005.

© COPYRIGHT 2005 By -

ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

変更

DESCRIPTION

DATE

DWN

APVD

P

LTR

SEE SHEET 1

-

-

-

PLUG CONNECTOR

RECEPTACLE
CONNECTOR
WITHOUT FLANGE TYPE

2 MAX

1.6 REF

2 MIN

SCREW

PLUG CONNECTOR

RECEPTACLE
CONNECTOR
WITH FLANGE TYPE

2 MAX

1.6 REF

2 MIN

MAX
ø6MATING CONDITION (REFERENCE)
(SCALE 2:1)

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN

CHK

APVD

PRODUCT SPEC
製品規格APPLICATION SPEC
取付適用規格

WEIGHT

CUSTOMER DRAWING

TE

TE Connectivity

NAME
名称HDMI 19 POS RECEPTACLE ASSY
SMT SHORT TYPE

SIZE

CAGE CODE

DRAWING NO
番号

A300779C=1903015

RESTRICTED TO


SCALE
尺度 4:1

SHEET

11 OF 12

REV

R

DIMENSIONS:
単位: 話
mmTOLERANCES UNLESS
OTHERWISE SPECIFIED:
一般公差0 PLC ±
1 PLC ±
2 PLC ±
3 PLC ±
4 PLC ±
ANGLES ±FINISH
仕上MATERIAL
材料

4

3

2

1

THIS DRAWING IS A CONTROLLED DOCUMENT.

NOT RELEASED FOR PUBLICATION

SEP, 2005.

COPYRIGHT 2005, By --

ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

P

LTR

DESCRIPTION

DATE

DWN

APVD

SEE SHEET 1

P/N:6-1903015-3

D

D

C





C

B


B

A

A



TRAY B (EMPTY)



THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: 單位: 英 mm	TOLERANCES UNLESS OTHERWISE SPECIFIED: 一般公差
0 PLC	±
1 PLC	±
2 PLC	±
3 PLC	±
4 PLC	±
ANGLES	±
FINISH 仕上	

DWN	CHK	APVD	PRODUCT SPEC 製品規格	APPLICATION SPEC 取付適用規格	WEIGHT	CUSTOMER DRAWING
-----	-----	------	----------------------	----------------------------	--------	------------------

NAME 名称	SIZE	CAGE CODE	DRAWING NO 番号	RESTRICTED TO
TE Connectivity	A3	00779	C-1903015	—
HDMI 19 POS RECEPTACLE ASSY SMT SHORT TYPE	SCALE 尺度	4:1	SHEET 12 OF 12	REV R