



Fuse-link, high speed, 10 A, AC 1200 V, DC 660 V, BS2692-1, 22 x 139 mm, BS

Catalog No. **TAC10**

Similar to illustration

Delivery program

Product range			Fuse
Basic function			Fuse-link
Field of application			high speed
Rated current	I	A	10
Rated voltage			AC 1200 V DC 660 V
Construction size			BS2692-1
Size			22 x 139 mm
Breaking Capacity		kA	63
usable for size/applications			traction
Standard/Approval			BS
Shape			offset bolted tags
Standards/Regulations			BS2692-1
Optional accessories			fuse-holder RSL63

Technical data ETIM 7.0

Circuit breakers and fuses (EG000020) / Low Voltage HRC fuse (EC000055)			
Electric engineering, automation, process control engineering / Electrical installation, device / Safety fuse inserts / Low-Voltage HRC fuse (ecl@ss10.0.1-27-14-20-05 [AFZ800015])			
Construction size			Other
Rated current		A	10
Rated voltage		V	1200
Voltage type			AC/DC
Rated switching capacity		kA	63
Utilization category			Other
Type of fuse status indicator			None
Insulated metal gripping lugs (IMGL)			No