

PRODUCT-DETAILS

TY525MR-0

TYRAP-PK-100PCS-BLACK-N66



General Information

Extended Product Type	TY525MR-0
Product ID	7TCG009450R0175
EAN	5414363065647
Catalog Description	TYRAP-PK-100PCS-BLACK-N66
Long Description	Cable Tie, Black Polyamide (Nylon 6.6) for Temperatures up to 85 Degrees Celsius (185 F) for Indoor Applications, UL/EN/CSA62275 Type 2/21S Rated for AH-2 Plenum and as a Flexible Cable and Conduit Support, Length of 185.67mm (7.31 Inches), Width of 4.67mm (0.184 Inches), Thickness of 1.09mm (0.043 Inches), Tensile Strength Rating of 222 Newtons (50 Pounds), Euroslot Packaging

Ordering

EAN	5414363065647
UPC	786210626383

Dimensions

Product Net Width	0.184 in 4.67 mm
Product Net Depth / Length	7.31 in 185.67 mm

Container Information

Package Level 1 Units	100 piece
Package Level 2 Units	10000 piece
Package Level 2 Width	15.4 in 391 mm
Package Level 2 Height	11 in 279 mm
Package Level 2 Depth / Length	23.6 in 599 mm

Technical UL/CSA

Flammability According to UL94	V-2
--------------------------------	-----

Additional Information

Brand / Label	Ty-Rap
Color	Black
Effective Date	19980621
Lock Type	Stainless Steel Barb
Material	Nylon/Polyamide 6.6
Number of Batteries	0
Product Name	TY-RAP FASTENING
Product Type	High Performance
Tensile Strength	50 lb 220 N
Thickness	0.043 in 1.09 mm

Certificates and Declarations (Document Number)

Data Sheet, Technical Information	TY525MR-0
Instructions and Manuals	TY525MR-0

Classifications

ETIM 6	EC000046 - Cable tie
ETIM 7	EC000046 - Cable tie
UNSPSC	39121703
WEEE Category	Product Not in WEEE Scope
IDEA Granular Category Code (IGCC)	5034 >> Cable ties

Categories

Low Voltage Products and Systems → Installation Products → Wire Management and Connectivity → Cable Ties

