


PXD306/050/01/1 Datasheet

Product Name // Box Style Rectangular IEC Distribution Unit PXD306 CEE7 Sheet VII Schuko Plug on 2M Cable 5 Shuttered Outlet Fused With Neon Indicator

 [View Product Page](#)



// Product Description:

- Box Style Rectangular IEC Distribution Units
 - 5 shuttered Outlets
 - Choice of power input depending on part code prefix:
 - PXD301: Single integral EN60320 Inlet
 - PXD303: BS1363 plug on 2M cable
- PXD306: CEE7 Sheet VII Schuko plug on 2M cable
 - Choice of unfiltered (part codes containing /050) or with EMI filter fitted (part codes containing /550)
 - Choice of 5mm x 20mm fuseholder and neon indicator (part codes containing /01) or Illuminated switch (part codes containing /07 are red Illuminated, part codes containing /08 are green Illuminated)
 - (PXD306 only available in unfiltered version with 5mm x 20mm fuseholder and neon indicator)
 - Mate with PX0686, PX0686/SE

// General Information:

Product Display Title:	Box Style Rectangular IEC Distribution Units
Product Family:	IEC Connectors
Product Series:	IEC Distribution Units
Body Material:	ABS
Current Max:	10A
Distribution Unit Light Colour:	Fused With Neon Indicator
Filter Type:	Unfiltered
Flamability Rating:	UL94V-0
Function:	Rectangular Units
Iec Connector Mates With:	PX0686,PX0686/SE
Inlet Type:	CEE7 Sheet VII Schuko Plug on 2M Cable
Max Operating Temperature:	+60°C
Min Operating Temperature:	-5°C
Number Of Contacts:	3 Contacts
Number Of Outlets:	5 Shuttered Outlet
Voltage Max:	250V

// Product PDF Links



// Product 3D CAD Model Links

