

Datasheet

Adjustable Jacket Slitter

- The AJS is designed for irregular cable diameters and thicknesses while providing protection to underlying conductors or material
- Professional-grade slitter designed for longitudinal, circumferential and mid-span operations on corrugated ALU and copper shielded cables, PE jackets(MDPE, HDPE) and tubes.
- The blade is high grade steel, precision ground, adjustable blade depth up to 6.3mm
- Blade fully retracts inside body for storage
- Cam-adjustable lever allows blade dig-in for mid-span operations
- Lever teeth designed for soft and hard jacket/covering applications
- Range for Longitudinal operation > 12.7 mm
- Range for Circumferential operation > 38 mm
- Range for Mid-span operation > 38 mm
- Made of rugged Aluminium



Type	Part nr	Size	Weight
AJS	7541163	221 x 52 x 39 mm	320 g