



jolas® EXALTER 9975

EN ISO 20345:2011 S3, SRC, HRO ASTM F2413-18 M/I/C SD 35 PR



Learn more

MID-CUT, WATER REPELLANT WITH LACES

This mid-cut safety shoe has the features you need for most work situations, such as PTC-textile nail protection, toecap in aluminum and high-grip Vibram Nitrile rubber outsole. The model provides extra ankle support and PORON® XRD™ shock-absorption prevents injuries to foot and back. The upper is water repellant, perfect for those who work in moist environments.

CHARACTERISTICS

- Highest level of protection
- Excellent grip
- Perfect fit
- Extra comfortable
- Excellent shock absorption

FUNCTIONS

- Double shock absorption zones
- Conforms with IEC 61340-5-1 (ESD)
- Heat-resistant outsole
- Oil-resistant outsole
- Anti-static properties
- Polstered shaft edge
- Ventilating insole
- Stabilizator
- Water repellent
- Ergonomically shaped
- Specially designed details
- Ankle support
- Soft
- Free from animal-derived materials



PREVENTS RISK OF
toe injuries, nail penetration, sprain injuries, antistatic
PRIMARY ENVIRONMENTS OF USE
outdoors, indoors, environments with risk for outsole
penetration, clean environments
SPECIFICATION

TYPE Safety footwear, Boots/Ankle boots
CATEGORY Cat. II
NAIL PROTECTION MATERIAL Plasma-treated
composite (PTC) textile
FITTING Regular
COLLECTION Exalter
UPPER MATERIAL Microfiber, Textile
TOECAP MATERIAL Aluminium
LINING MATERIAL Polyester
INSOLE FX3 Supreme
INNERSOLE MATERIAL Textile, Soft EVA, Rigid EVA,
Polyester-based conductive thread, Neo foam, Poron®
XRD®
MIDSOLE MATERIAL PU midsole
OUTSOLE MATERIAL Nitrile rubber outsole
FASTENING Laces
COLOUR Black, Red
NET WEIGHT, (SIZE 42) 1.26 kg

COMPLIANCE



Cat. II

EN ISO 20345:2011
S3, SRC, HRO



ASTM F2413-18
M/I/C
SD 35 PR

TP TC 019:2011



ÖNORM Z 1259



DGUV 112-191

FEATURES



Anti-static
properties



Ergothan Shock
Absorption System



ESD



Aluminium toecap



Oil-resistant
outsole



Heat-resistant
outsole



Water repellent



Nail protection in
plasma-treated
composite (PTC)
textile



Stabilizer

SIZE				ARTICLE NUMBER	EAN
EU	UK	US M	US W		
34	1½	2½	3½	9975-34	6408487512292
35	2	3½	4	9975-35	6408487512315
36	3	4	5	9975-36	6408487512339
37	4	5	6	9975-37	6408487512353
38	5	5½	6½	9975-38	6408487512377
39	6	6½	7½	9975-39	6408487512391
40	6½	7½	8½	9975-40	6408487512414
41	7	8	9	9975-41	6408487512438
42	8	9	10	9975-42	6408487512452
43	9	9½	11	9975-43	6408487512476
44	10	10½	11½	9975-44	6408487512490
45	10½	11	12½	9975-45	6408487512513
46	11	12	13	9975-46	6408487512537
47	12	13	14	9975-47	6408487512551

ejendals

Limavägen 28, SE-793 32 Leksand, Sweden
Phone +46 (0) 247 360 00 | info@ejendals.com | order@ejendals.com