

Terminals and Splices

Ring and Spade Tongue Terminals

AMP

(Tyco Electronics P/N: 342141-1)



Searchable Features:

Brand:	AMP
Terminal Shape:	Ring Tongue
Receptacle Style:	Straight
Body Style:	PLASTI-GRIP
Barrel Type:	Closed Barrel
Wire/Cable Type:	Regular Wire
Wire Range (mm [AWG]):	1.00-2.60 ² [16-14]
Insulation:	Yes
Insulation Support:	Non-Insulation Support
Insulation Diameter (mm [in]):	4.29 [.169] Max.
Stud Size:	M2.5
Stud Diameter (mm [in]):	3.00 [0.118]
Shape:	RING-043
Heavy Duty:	Standard
Packaging Method:	Loose Piece
Material:	Copper
Finish:	Tin

Other Properties:

Voltage (VAC):	600
Color:	Blue
Insulation Material:	Vinyl
Insulation Sleeve Material:	PVC
CERTI-CRIMP Hand Tool:	47387-7, 525691-0 (Great Britain Tool)

[Copyright](#) and [Privacy Statement](#)

Visit [Tyco International, Ltd.](#)