

213.53.063 -1/+9 bar G1/4B lower mount

Bourdon tube pressure gauges, liquid filled,

Item number: 9021922

Quantity: 1 pcs.

Order code: 213.53-C-BV410Z-GB-UZZZ-ZZZ 53 31ABZNZA ZS-ZZZ
DIAL-IAZ1ZZZZZZZZZ1Z- ZZ11Z4ZZZZ
LABEL-E01DE-ZZZZZ

Overview: 213.53.063 -1/+9 bar G1/4B lower mount
class 1.6

Window: plastic, clear

Case filling fluid: glycerine

standard packing

S *EN 837-1* *Cl.1.6* *WIKA*

Details: Bourdon tube pressure gauges, liquid filled,
stainless steel case, model 213.53.050/063

Model: 213.53

Specifications according to data sheet: PM 02.12

Measuring system: copper alloy

Case: stainless steel 1.4301

Case: Crimp ring case (version 53)

Nominal size: 063 mm

Scale range: -1...+9 bar

Process connection: G 1/4 B

Connector location: lower mount

Accuracy class: class 1.6

Overpressure safe: standard

Case filling fluid: glycerine

Pointer: plastic, black

Window: plastic, clear

Packaging: standard packing

Dial: plastic white without stop pin

Dial description:

Pressure Gauge Standard: International (standard Europe)

color for 1.scale (outside): black

dial background: White

Manufacturer logo: *WIKA*

norm-mark on dial: *EN 837-1*

safetymark on dial: *S*

accuracy class on dial: *Cl.1.6*