



## Ring ratchet insert adaptor 717

717



Product no. **58170122**  
GTIN **4018754348510**  
Model **717/22**



Label.

Ring ratchet insert adaptor 22mm Tool holders 9 x 12

## Product highlights.



PRODUCT IMAGE  
IN PROGRESS

### Fine-tooth ring ratchet.

The high level of accuracy is achieved by flat transducers and a special technology for immediate data processing directly in the transducer. Thanks to an integrated measurement amplifier, the testing device is resistant to bending moments and transverse forces.



PRODUCT IMAGE  
IN PROGRESS

### For confined spaces.

This ring ratchet insert adaptor enables precise work with a working angle of just 5°. Thanks to its slim design, it is particularly well-suited for use in tight and hard-to-reach areas where larger movements are not possible.



PRODUCT IMAGE  
IN PROGRESS

### Safe switching.

The high level of accuracy is achieved by flat transducers and a special technology for immediate data processing directly in the transducer. Thanks to an integrated measurement amplifier, the testing device is resistant to bending moments and transverse forces.



PRODUCT IMAGE  
IN PROGRESS

### Safe and durable.

The high level of accuracy is achieved by flat transducers and a special technology for immediate data processing directly in the transducer. Thanks to an integrated measurement amplifier, the testing device is resistant to bending moments and transverse forces.

## Technologies and features.



### High Performance Quality (HPQ®)

Our HPQ® tool is made of wear-resistant high-performance steel, yet is thin-walled and lightweight. It withstands high torques and is ideal for work in confined spaces such as turbines.

## Technical drawing.



## Technical attributes.

|                                               |                             |
|-----------------------------------------------|-----------------------------|
| Number of teeth                               | 72                          |
| Working angle                                 | 5 °                         |
| Width mm (b)                                  | 42 mm                       |
| Size square socket<br>[internal square drive] | 9 x 12 mm                   |
| Height mm (h)                                 | 13,8 mm                     |
| Alloy                                         | HPQ® high performance steel |
| max. torque                                   | 160 N·m                     |
| S                                             | 52 mm                       |
| Width across flats [mm]                       | 22 mm                       |

## Logistics data.

|                                   |                         |
|-----------------------------------|-------------------------|
| Depth mm (IFS)                    | 88                      |
| Width mm (IFS)                    | 42                      |
| Height mm (IFS)                   | 16                      |
| WEEE/ElektroG                     | nicht ear-pflichtig     |
| Length (packed, mm)               | 98                      |
| Width (packed, mm)                | 65                      |
| Height (packed, mm)               | 18                      |
| Volume (packed, dm <sup>3</sup> ) | 0.11466 dm <sup>3</sup> |
| Art. no.                          | 58170122                |
| Weight (gross, kg)                | 0,170                   |
| Weight PAP (kg)                   | 0,000                   |
| Weight PVC (kg)                   | 0,004                   |
| GTIN                              | 4018754348510           |
| Country of origin AWR             | CHINA                   |
| Region of origin                  | Ausländischer Ursprung  |
| Customs tariff no.                | 82042000                |
| Packing standard                  | 1                       |
| Weight                            | 166 g                   |

## Variants.

| Art. no. | Model no. (ERP) | Description                                         | GTIN          |
|----------|-----------------|-----------------------------------------------------|---------------|
| 58170108 | 717/8           | Ring ratchet insert adaptor 8mm Tool holders9 x 12  | 4018754348619 |
| 58170110 | 717/10          | Ring ratchet insert adaptor 10mm Tool holders9 x 12 | 4018754348626 |
| 58170112 | 717/12          | Ring ratchet insert adaptor 12mm Tool holders9 x 12 | 4018754348411 |
| 58170113 | 717/13          | Ring ratchet insert adaptor 13mm Tool holders9 x 12 | 4018754348428 |
| 58170117 | 717/17          | Ring ratchet insert adaptor 17mm Tool holders9 x 12 | 4018754348435 |
| 58170119 | 717/19          | Ring ratchet insert adaptor 19mm Tool holders9 x 12 | 4018754348442 |
| 58170122 | 717/22          | Ring ratchet insert adaptor 22mm Tool holders9 x 12 | 4018754348510 |

## GTIN.



## Images.



STAHLWILLE Eduard Wille GmbH & Co. KG

Lindenallee 27 · 42349 Wuppertal · Germany · Phone: +49 202 4791-0 · Fax: +49 202 4791-393

info@stahlwille.de · www.stahlwille.com

© STAHLWILLE Eduard Wille GmbH & Co. KG, Wuppertal