



719-9891 with filled inner lift-out

Meets EN 61340-5-1

Features:

- Static dissipative
- Made of polypropylene
- Includes inner lift-out tray for added storage
- Clean, no surface coating to rub off, washable
- Size: 14.5" (370mm) x 7.5" (190mm) x 5" (135mm)
- Made in America

Electrical Properties*:

1 x 10⁵ ohms to < 1 x 10¹¹ ohms per IEC 61340-2-3

*Depends on test method and device used

Item	Description
719-9891	Tool Box, Dissipative, Yellow

"It should be understood that any object, item, material or person could be a source of static electricity in the work environment. Removal of unnecessary nonconductors, replacing nonconductive materials with dissipative or conductive materials and grounding all conductors are the principle methods of controlling static electricity in the workplace, regardless of the activity." [ESD Handbook ESD TR20.20-2008 section 2.4 Sources of Static Electricity]

Unless otherwise noted, tolerance ±10%
Specifications and procedures subject to change without notice.



Made in the
United States of America



Yellow Dissipative Tool Box

RS COMPONENTS LTD.
BIRCHINGTON ROAD, CORBY,
NORTHANTS, NN17 9RS, UK

Drawing Number
RS-719-9891

DATE:
August
2014