

19 L 13

Socket 1/2"

hexagon UD-profile, long pattern

Code	ETIM
1718762	EC002203
EAN	UNSPSC
4010886849538	27-11-17-04
Country of origin	eCl@ss
Germany	21-04-02-18
Customs tariff number	
82042000	



Article description

- Acc. to DIN 3124, ISO 2725-1
- Square drive as per DIN 3120 - C 12,5, ISO 1174, with ball retention groove
- Manually operated, with non-slip cross knurling
- GEDORE vanadium steel 31CrV3, polished, chrome-plated

Article information

Contents (Qty of pieces)	1	Standard	DIN 3124 ISO 2725-1 DIN 3120 - C 12,5 ISO 1174
Net weight [kg]	0,098 kg	Width across flats 1 [mm]	13
Total length [mm]	77 mm	Backup	Ball Catching Cricket
Total width [mm]	22,5 mm	Insert-Ø 1	19,2 mm
Surface	polished, chrome-plated	Working length	77,0 mm
Material	Chrome-vanadium steel	Insert-Ø 2	22,5 mm
Drive connector square female (metric)	12,5 mm	Operating depth	16,0 mm
Drive connector square female [inch]	1/2"		