



182.72.104.66RPNAEinstell-Nadellager

Aligning needle roller bearings RPNA40/55-XL (Series RPNA) without inner ring

The datasheet is only an overview of dimensions and basic load ratings of the selected product. Please always observe all the guidelines in these overview pages. Further information is given on many products under the menu item "Description". You can also order comprehensive information via the Catalogue ordering system (https://www.schaeffler.de/content.schaeffler.de/en/news_media/index.jsp) or by telephone on +49 (91 32) 82 - 28 97.

Fw	40 mm
D	55 mm
C	20 mm Tolerance: +/-0,5
D1	50,5 mm
rmin	0,8 mm
m	141 g Mass
Cr	29500 N Basic dynamic load rating, radial
C0r	47000 N Basic static load rating, radial
Cur	8300 N Fatigue limit load, radial
ng	11400 1/min Limiting speed

