

Add-on block 2P 63A 30mA HI

Technical Properties

Number of poles	2 P
Rated current	63 A
Rated residual operating current	30 mA
Residual current type	HI
Number of modules	2
Frequency	50 Hz
Rated operational voltage Ue	230 V
Operating temperature	-5 to 40 °C