



verso maintenance trolley with double cupboard & lino top. Featuring a robust, fully welded steel housing with double, independent, storage sections, push - pull handles and 125mm diameter castors. Double cupboard section with twin, reinforced, doors and 2 galvanised steel shelves (75kg U.D.L. per shelf. Finished in durable powder coat paint in RAL 7035 light grey / RAL 7035 light grey. WxDxH: 1050x600x980mm

Breite [mm]: 1050
Tiefe [mm]: 600
Höhe [mm]: 980
Bruttogewicht [kg]: 73.96
EAN-Code: 5039350117743
Zolltarifnummer UK: 94032080
Ursprungsland: GB

Produkteigenschaften

Product surface	Powder coated
Product material	Sheet steel
Main colour	Light grey
Main RAL colour	RAL 7035
Secondary colour	Light grey
Secondary RAL colour	RAL 7035

Artikelbeschreibungen

Product brand	verso
---------------	-------

Schubladen

Drawer load capacity [kg]	50
---------------------------	----

Schrank, Gehäuse, Werkbank und EAP

Worktop/housing top type	Lino
Shelf load capacity [kg]	75



Door type	Plain
Door height 1 [mm]	725