

**ZM80** **Precision locknut**

Precision locknut ZM, accessory ZM..

Technical information**Main Dimensions & Performance Data**

d	M80X2	Thread
D	105 mm	Outside diameter
h	18 mm	Height
M _A	15 Nm	Mounting torque set screw
F _{aB}	355,000 N	Breaking load, axial
M _L	285 Nm	Breakawag
M _{AL}	160 Nm	Mounting torque reference
M _M	11.2 kg*cm ²	Mass moment of inertia
≈m	0.492 kg	Weight

Dimensions

d ₁	95 mm	Plant diameter outside
t	3.5 mm	Hight retaining slot
b	8 mm	Width retaining slot
c	9 mm	Distance bore
m	M8	Threaded - threaded pin