

3.5" TFT Test Monitor

Art. no. TVAC10100

Page 1 of 2



- Measurement of AC/DC voltage and video signal
- Continuity measurement
- Zoom/PTZ camera control (PELCO D/P)
- Graphical on-screen display (OSD)
- Battery operation for up to 4 hours

The new ABUS Security-Center test monitor is the ideal tool for all video projects. The monitor is easy to transport and thus delivers the desired performance data wherever needed - video image, voltage, line connectivity. A special highlight is that you can immediately check the images on the monitor while you are adjusting the PTZ camera. This makes adjustments for different positions a lot easier.

3.5" TFT Test Monitor

Art. no. TVAC10100

Page 2 of 2

Technical Data:

Dimensions	(W x H x D) 156 x 90 x 38 mm
Connection type	BNC, audio, RS-485, cable 1, cable 2
Horizontal/vertical viewing angle	120 x 100 °
Picture format	4:3
Screen diagonal	3.5 "
Width	156 mm
Display surface	Matte
Color levels	16.7 MIO
Frequency range	60 Hz (P) / 50 Hz (N) GHz
Functions	AC / DC voltage measurement, cable continuity test, speed dome test, video level measurement, audio test
Housing material	Plastic
Brightness	300 cd/m ²
Height	90 mm
Contrast ratio	350:1

Length	38 mm
Loudspeaker	1
Max. operating temperature	45 °C
Min. operating temperature	0 °C
Monitor type	Test monitor
Net weight	0.29 kg
Reaction time	25 ms
Signal detection	Automatic
DC voltage supply	9 V
OSD language	multilingual
Power consumption	400 mA
Video system	PAL / NTSC