



SPEED SLOT® BI-METAL HOLE SAW
WITH T3 TECHNOLOGY™

1 PER BOX	DESCRIPTION		USE ARBOR		EAN
ITEM NO.	in	mm	SNAP-BACK™	STANDARD	
0099L	9L	14mm	5L	1L, 4L, 5L	082472300093
3001010L	10L	16mm	5L	1L, 4L, 5L	082472300109
3001111L	11L	17mm	5L	1L, 4L, 5L	082472300116
3001212L	12L	19mm	5L	1L, 4L, 5L	082472300123
3009820MMHS	20L	20mm	5L	1L, 4L, 5L	082472300987
3001313L	13L	21mm	5L	1L, 4L, 5L	082472300130
3001414L	14L	22mm	5L	1L, 4L, 5L	082472300147
3001515L	15L	24mm	5L	1L, 4L, 5L	082472300154
3001616L	16L	25mm	5L	1L, 4L, 5L	082472300161
3001717L	17L	27mm	5L	1L, 4L, 5L	082472300178
3001818L	18L	29mm	5L	1L, 4L, 5L	082472300185
3001919L	19L	30mm	5L	1L, 4L, 5L	082472300192
3002020L	20L	32mm	2L, 6L	2L, 3L, 6L	082472300208
3002121L	21L	33mm	2L, 6L	2L, 3L, 6L	082472300215
3002222L	22L	35mm	2L, 6L	2L, 3L, 6L	082472300222
3002323L	23L	37mm	2L, 6L	2L, 3L, 6L	082472300239
3002424L	24L	38mm	2L, 6L	2L, 3L, 6L, 7L	082472300246
3002525L	25L	40mm	2L, 6L	2L, 3L, 6L, 7L	082472300253
3002626L	26L	41mm	2L, 6L	2L, 3L, 6L, 7L	082472300260
3002727L	27L	43mm	2L, 6L	2L, 3L, 6L, 7L	082472300277
3002828L	28L	44mm	2L, 6L	2L, 3L, 6L, 7L	082472300284
3002929L	29L	46mm	2L, 6L	2L, 3L, 6L, 7L	082472300291
3003030L	30L	48mm	2L, 6L	2L, 3L, 6L, 7L	082472300307
3003232L	32L	51mm	2L, 6L	2L, 3L, 6L, 7L	082472300321
3003333L	33L	52mm	2L, 6L	2L, 3L, 6L, 7L	082472300338
3003434L	34L	54mm	2L, 6L	2L, 3L, 6L, 7L	082472300345
3003636L	36L	57mm	2L, 6L	2L, 3L, 6L, 7L	082472300369
3003838L	38L	60mm	2L, 6L	2L, 3L, 6L, 7L	082472300383
1816242	39L	62mm	2L, 6L	2L, 3L, 6L, 7L	885363008968
3004040L	40L	64mm	2L, 6L	2L, 3L, 6L, 7L	082472300406
3004141L	41L	65mm	2L, 6L	2L, 3L, 6L, 7L	082472300413
3004242L	42L	67mm	2L, 6L	2L, 3L, 6L, 7L	082472300420
3004343L	43L	68mm	2L, 6L	2L, 3L, 6L, 7L	082472300437
3004444L	44L	70mm	2L, 6L	2L, 3L, 6L, 7L	082472300444
3004646L	46L	73mm	2L, 6L	2L, 3L, 6L, 7L	082472300468
3004848L	48L	76mm	2L, 6L	2L, 3L, 6L, 7L	082472300482
3005050L	50L	79mm	2L, 6L	2L, 3L, 6L, 7L	082472300505
3005252L	52L	83mm	2L, 6L	2L, 3L, 6L, 7L	082472300529
3005454L	54L	86mm	2L, 6L	2L, 3L, 6L, 7L	082472300543
3005656L	56L	89mm	2L, 6L	2L, 3L, 6L, 7L	082472300567
3005858L	58L	92mm	2L, 6L	2L, 3L, 6L, 7L	082472300581
3006060L	60L	95mm	2L, 6L	2L, 3L, 6L, 7L	082472300604
3006262L	62L	98mm	2L, 6L	2L, 3L, 6L, 7L	082472300628
3006464L	64L	102mm	2L, 6L	2L, 3L, 6L, 7L	082472300642
3006666L	66L	105mm	2L, 6L	2L, 3L, 6L, 7L	082472300666
3006868L	68L	108mm	2L, 6L	2L, 3L, 6L, 7L	082472300680
3007070L	70L	111mm	2L, 6L	2L, 3L, 6L, 7L	082472300703
3007272L	72L	114mm	2L, 6L	2L, 3L, 6L, 7L	082472300727
3007474L	74L	118mm	2L, 6L	2L, 3L, 6L, 7L	082472300741
3007676L	76L	121mm	2L, 6L	2L, 3L, 6L, 7L	082472300765
3008080L	80L	127mm	2L, 6L	2L, 3L, 6L, 7L	082472300802
1816243	83L	133mm	2L, 6L	2L, 3L, 6L, 7L	885363008975
3008888L	88L	140mm	2L, 6L	2L, 3L, 6L, 7L	082472300888
3009696L	96L	152mm	2L, 6L	2L, 3L, 6L, 7L	082472300963
3106106L	*106L	168mm	2L, 6L	2L, 3L, 6L, 7L	5706915081633
3112112L	*112L	177mm	2L, 6L	2L, 3L, 6L, 7L	5706915081640
3132132L	*132L	210mm	2L, 6L	2L, 3L, 6L, 7L	5706915081657

*T1 bi-metal hole saw design



Designed for Drilling Wood & Metal

IMPROVED METAL CUTTING PERFORMANCE

Increased wall thickness improves durability and minimizes tooth loss. Optimized tooth design penetrates metal with ease

FAST, EFFICIENT CUTTING IN WOOD

Larger, sharper teeth remove more wood for fast cutting

EASY PLUG REMOVAL

SPEED SLOT® staircase design for fast, easy plug ejection

*vs Prior LENOX Generation



BI-METAL HOLE SAW CROSS REFERENCE CHART

ITEM NO.	DIAMETER	BOSCH®	MILWAUKEE®	WILPU®	DeWALT®
300099L	14mm	2 608 594 195	49560002	30014 00101	DT90295
3001010L	16mm	2 608 594 196	49560012	30016 00101	DT90296
3001111L	17mm	2 608 594 197	49560014	30017 00101	DT90297
3001212L	19mm	2 608 594 198	49560023	30019 00101	DT90298
3009820MMHS	20mm	2 608 594 199	49560024	30020 00101	DT90299
3001313L	21mm	2 608 594 200	49560027	30021 00101	DT90300
3001414L	22mm	2 608 594 201	49560032	30022 00101	DT90301
3001515L	24mm	2 608 594 202	49560037	30024 00101	DT90302
3001616L	25mm	2 608 594 203	49560043	30025 00101	DT90303
3001717L	27mm	2 608 594 204	49560047	30027 00101	DT90304
3001818L	29mm	2 608 594 205	49560052	30029 00101	DT90305
3001919L	30mm	2 608 594 206	49560057	30030 00101	DT90306
3002020L	32mm	2 608 594 207	49560062	30032 00101	DT90307
3002121L	33mm	2 608 594 208	49560067	30033 00101	DT90308
3002222L	35mm	2 608 594 209	49560072	30035 00101	DT90309
3002323L	37mm	2 608 594 210	49560077	30037 00101	DT90310
3002424L	38mm	2 608 594 211	49560082	30038 00101	DT90311
3002525L	40mm	2 608 594 212	49560087	30040 00101	DT90312
3002626L	41mm	2 608 594 213	49560092	30041 00101	DT90313
3002727L	43mm	2 608 594 214	49560097	30043 00101	DT90314
3002828L	44mm	2 608 594 215	49560102	30044 00101	DT90315
3002929L	46mm	2 608 594 216	49560107	30046 00101	DT90316
3003030L	48mm	2 608 594 217	49560112	30048 00101	DT90317
3003232L	51mm	2 608 594 218	49560117	30051 00101	DT90318
3003333L	52mm	2 608 594 219	49560122	30052 00101	DT90319
3003434L	54mm	2 608 594 220	49560127	30054 00101	DT90320
3003636L	57mm	2 608 594 222	49560132	30057 00101	DT90322
3003838L	60mm	2 608 594 224	49560142	30060 00101	DT90323
1816242	62mm	—	—	—	—
3004040L	64mm	2 608 594 225	49560147	30064 00101	DT90324
3004141L	65mm	2 608 594 226	49560153	30065 00101	DT90325
3004242L	67mm	2 608 594 227	49560158	30067 00101	DT90326
3004343L	68mm	2 608 594 228	49560159	30068 00101	DT90327
3004444L	70mm	2 608 594 229	49560163	30070 00101	DT90328
3004646L	73mm	2 608 594 230	49560167	30073 00101	DT90329
3004848L	76mm	2 608 594 231	49560173	30076 00101	DT90330
3005050L	79mm	2 608 594 232	49560177	30079 00101	DT90331
3005252L	83mm	2 608 594 233	49560183	30083 00101	DT90332
3005454L	86mm	2 608 594 234	49560187	30086 00101	DT90333
3005656L	89mm	2 608 594 235	49560193	30089 00101	DT90334
3005858L	92mm	2 608 594 236	49560197	30092 00101	DT90335
3006060L	95mm	2 608 594 237	49560203	30095 00101	DT90336
3006262L	98mm	2 608 594 238	49560207	30098 00101	DT90337
3006464L	102mm	2 608 594 239	49560213	30102 00101	DT90338
3006666L	105mm	2 608 594 240	49560217	30105 00101	DT90339
3006868L	108mm	2 608 594 241	—	30108 00101	DT90340
3007070L	111mm	2 608 594 242	49560227	30111 00101	DT90341
3007272L	114mm	2 608 594 243	49560233	30114 00101	DT90342
3007474L	118mm	2 608 594 244	—	—	—
3007676L	121mm	2 608 594 244	49560237	30121 00101	DT90343
3008080L	127mm	2 608 594 245	49560243	30127 00101	DT90344
1816243	133mm	2 608 594 246	49560244	30133 00101	—
3008888L	140mm	2 608 594 247	49560247	30140 00101	DT90345
3009696L	152mm	2 608 594 248	49560253	30152 00101	DT90346
3106106L	*168mm	2 608 594 249	4932399886	30168 00101	DT90347
3112112L	*177mm	2 608 594 250	4932399887	30177 00101	DT90348
3132132L	*210mm	2 608 594 251	4932399889	30210 00101	DT90349

*T1 bi-metal hole saw design

Bosch® is a Registered Trademark of Robert Bosch GmbH
Milwaukee® is a registered trademark of Milwaukee Electric Tool Corp.

WILPU® is a registered trademark of Wilh. Putsch GmbH & Co. Kg
DeWALT® is a Registered Trade Mark of The Black & Decker Corporation





SPEED SLOT® BI-METAL HOLE SAW WITH T3 TECHNOLOGY™ KITS

Convenient Storage for Trade-Specific Uses

- DURABLE**
Durable construction resists damage caused by drops and tough workplace environments
- SECURE**
Latches close case tightly and securely
- LONG LASTING**
Metal latches and metal pin hinges won't break or tear



COMPACT KIT
4-11/16"h x 7-1/2"w

MEDIUM KIT
8"h x 11"w

LARGE KIT
10"h x 14"w

CONTRACTOR'S KITS



1768793
9 PIECE KIT
22, 25, 32, 35, 38, 44, 54mm,
Arbors: 5L, 6L



1768795
17 PIECE KIT
16, 19, 22, 25, 29, 32, 35, 38, 44, 51, 64, 76mm,
Arbors: 1L, 2L, 3 x 4321 Pilot Drill Bits



1768698
26 PIECE KIT-BIG DADDY™
19, 22, 25, 29, 35, 38, 44, 51, 54, 57, 64, 68, 76, 83, 86, 92, 95, 105, 114, 121mm,
Standard Arbors: 1L, 2L, 5L,
2 x 4321 Pilot Drill Bits, 1 x 56PD Pilot Drill Bit

ELECTRICIAN'S KITS



1768662
8 PIECE KIT
16, 20, 25, 32, 38, 51mm,
Arbors: 1L, 2L



1768668
9 PIECE KIT
16, 20, 25, 32, 41, 51, 64mm,
Arbors: 1L, 2L



1768696
10 PIECE KIT
22, 29, 35, 44, 51, 64mm,
Arbors: 2L, 5L, 1 x 4321 Pilot Drill Bit, 1 x Arbor Adapter



1768556
17 PIECE KIT
16, 19, 22, 25, 29, 32, 35, 38, 44, 51, 68, 76mm,
Arbors: 1L, 2L, 2 x 4321 Pilot Drill Bits, 1 x 56PD Pilot Drill Bits



1768695
17 PIECE KIT
19, 22, 29, 35, 44, 51, 64, 68, 76, 92, 105, 121mm,
Arbors: 2L, 5L, 2 x 4321 Pilot Drill Bits, 1 x 56PD Pilot Drill Bit



1768559
21 PIECE KIT
19, 22, 25, 29, 35, 38, 44, 51, 57, 68, 76, 83, 92, 95, 105, 121mm,
Arbors: 1L, 2L, 2 x 4321 Pilot Drill Bits, 1 x 56PD Pilot Drill Bits

PLUMBER'S KITS



1768436
LENOX® 6PC HOLE SAW KIT INT600P PLUMBERS
19, 22, 29, 38, 44, 68mm,
Arbors: 2L, 5L, 1 x Arbor Adapter



1768794
LENOX® 6PC HOLE SAW KIT INT600P PLUMBER
19, 22, 29, 38, 44, 57mm
Arbors: 2L, 5L, 1 x 4321 Pilot Drill Bit, 1 x Arbor Adapter



SNAP-BACK™ ARBORS

No Tools. No Adaptors. No Screwing Around.

- QUICK CHANGE**
Faster and easier to engage/disengage hole saw
- PREVENTS THREADS FROM STRIPPING**
Drives off pins, not threads
- NO TOOLS NEEDED**
Prevents hole saw from locking on arbor
- NO ADAPTOR REQUIRED**
Standard Arbor threads directly into all hole saws
- EASIER PLUG REMOVAL**



ITEM NO.	DESCRIPTION	FITS HOLE SAWS	SIZES		THREAD SIZE	SHANK TYPE	SHANK SIZE	
			in	mm			in	mm
1768811	2L Hole Saw ARBOR SNAP-BACK™	20L-132L	1-1/4–8-17/64	31.8–210	5/8–18	Solid Hex	1/2 & larger	12.7 & larger
1768812	5L Hole Saw ARBOR SNAP-BACK™	9L-19L	9/16–1-3/16	14–30	1/2–20	Solid Hex	3/8 & larger	9.5 & larger
1768813	6L Hole saw ARBOR SNAP-BACK™	20L-132L	1-1/4–8-17/64	31.8–210	5/8–18	Solid Hex	3/8 & larger	9.5 & larger





STANDARD ARBORS & ACCESSORIES

Arbors & Accessories for All Your Drilling Needs

ADDED DURABILITY

Hardened carbon steel for strength

STARTS ON CONTACT

Split point pilot drill for faster penetration and less walking



LENOX 6L Standard Arbor with quick change feature (1779805)

ITEM NO.	DESCRIPTION	FITS HOLE SAWS	SIZES		SHANK TYPE	SHANK SIZE		PRIMARY FEATURE
			in	mm		in	mm	
1779774	1L Holesaw ARBOR 4.25	9L–19L	9/16–1-3/16	14.3–30.2	Hollow Hex	1/2 & larger	12.7 & larger	Adjustable pilot bit
1779801	2L Holesaw ARBOR 4.25	20L–132L	1-1/4–8-17/64	31.8–210	Solid Hex	1/2 & larger	12.7 & larger	Use for enlarging holes
1779802	3L Holesaw ARBOR 3.25	20L–132L	1-1/4–8-17/64	31.8–210	Solid Hex	1/2 & larger	12.7 & larger	Solid shank
1779803	4L Holesaw ARBOR 4.25	9L–19L	9/16–1-3/16	14.3–30.2	3 Sided	1/4 & larger	6.4 & larger	Adjustable pilot bit, 3 flats on shank
1779804	5L Holesaw ARBOR 3.25	9L–19L	9/16–1-3/16	14.3–30.2	Hex	3/8 & larger	9.5 & larger	Use for 9A-19A arbored hole saws
1779805	6L ARBOR 3.25	20L–132L	1-1/4–8-17/64	31.8–210	Hex	3/8 & larger	9.5 & larger	Quick change arbor
1779806	7L ARBOR 3.25	24L–132L	1-1/2–8-17/64	31.8–210	Hex	3/8 & larger	9.5 & larger	Plug ejection feature

PROD NO	DESCRIPTION	CHUCK SIZE		FITS ARBOR	
		IN	MM	SNAP BACK™	SOLID HEX
1779771	4-1/4" Pilot Drill (1 pack)	1/4	6.4	2L, 5L, 6L	1L, 2L, 3L, 4L, 5L, 6L, 7L
1779810	3-1/4" Pilot Drill (1 pack)	1/4	6.4	2L, 5L, 6L	1L, 2L, 3L, 4L, 5L, 6L, 7L
LXAH9314CTPB	3-1/4" Carbide Tipped Pilot Drill (1 pack)	1/4	6.4	2L, 5L, 6L	1L, 2L, 3L, 4L, 5L, 6L, 7L
LXAH9414CTPB	4-1/4" Carbide Tipped Pilot Drill (1 pack)	1/4	6.4	2L, 5L, 6L	1L, 2L, 3L, 4L, 5L, 6L, 7L
30857AA1	Standard Arbor Adaptor (1 pack)	—	—	5L	1L, 4L, 5L
3084818X	18" Extension (1 pack)	1/2 & larger	12.7 & larger	2L	1L, 2L, 3L
3084712X	12" Extension (1 pack)	1/2 & larger	12.7 & larger	2L	1L, 2L, 3L

* Fits arbored hole saws



LENOX® DIAMOND™ HOLE SAWS

More Holes. Less Time.

LONG LASTING

Continuous, brazed edge lasts longer in tile and stone

DURABLE

Robust design for greater durability in tough applications

FAST, EASY CUTTING

Low torque, little pressure required

EASIER PLUG REMOVAL

Over-sized slot in hole saw for easy plug removal

USE STANDARD ARBOR, SNAP-BACK™ ARBOR FOR BEST RESULTS

1 PER PACK ITEM NO.	DESCRIPTION	USE ARBOR STANDARD	EAN
10507823	DIAMOND™ Hole Saw 19mm	1L, 4L, 5L	5706915078237
10507824	DIAMOND™ Hole Saw 20mm	1L, 4L, 5L	5706915078244
10507825	DIAMOND™ Hole Saw 22mm	1L, 4L, 5L	5706915078251
10507826	DIAMOND™ Hole Saw 25mm	1L, 4L, 5L	5706915078268
10507827	DIAMOND™ Hole Saw 29mm	1L, 4L, 5L	5706915078275
10507828	DIAMOND™ Hole Saw 32mm	2L, 3L, 6L, 7L	5706915078282
10507829	DIAMOND™ Hole Saw 35mm	2L, 3L, 6L, 7L	5706915078299
10507830	DIAMOND™ Hole Saw 38mm	2L, 3L, 6L, 7L	5706915078305
10507831	DIAMOND™ Hole Saw 44mm	2L, 3L, 6L, 7L	5706915078312
10507832	DIAMOND™ Hole Saw 48mm	2L, 3L, 6L, 7L	5706915078329
10507833	DIAMOND™ Hole Saw 51mm	2L, 3L, 6L, 7L	5706915078336
10507834	DIAMOND™ Hole Saw 54mm	2L, 3L, 6L, 7L	5706915078343
10507835	DIAMOND™ Hole Saw 57mm	2L, 3L, 6L, 7L	5706915078350
10507836	DIAMOND™ Hole Saw 60mm	2L, 3L, 6L, 7L	5706915078367
10507837	DIAMOND™ Hole Saw 64mm	2L, 3L, 6L, 7L	5706915078374
10507838	DIAMOND™ Hole Saw 68mm	2L, 3L, 6L, 7L	5706915078381
10507839	DIAMOND™ Hole Saw 76mm	2L, 3L, 6L, 7L	5706915078398
10507840	DIAMOND™ Hole Saw 83mm	2L, 3L, 6L, 7L	5706915078404
10507841	DIAMOND™ Hole Saw 102mm	2L, 3L, 6L, 7L	5706915078411
10507842	DIAMOND™ Hole Saw 114mm	2L, 3L, 6L, 7L	5706915078428

