

Previously known as: MICROGARD® 2000 STANDARD Trousers - Model 301

Superior protection from low hazard liquid spray and fine particulates with bound seams for improved overall protection..

DESIGN

MICROGARD® 2000 range is designed to allow water vapour (perspiration) to escape from the suit yet will withstand saturation of liquid chemicals and filter 100% of particulates down to 0.01 microns in size.

BOUND SEAMS

Superior strength, liquid and particle barrier

PANTS FEATURES

- Elasticsation to waist and ankles
- Bound seams

COLOURS

White

SIZES

S - 3XL



Industries

- Life Sciences
- Metal fabrication
- Food Processing

Applications

- Clean room cleaning and preparing
- Production line support & maintenance
- Maintenance of plant and machines
- Veterinary Services
- Cleaning of plant and machines
- Body painting including surface inspection


KEY FEATURES & BENEFITS

- Proven protective barrier to low concentration liquid chemicals, liquid & particulate biological hazards
- Comfortable to wear featuring moisture vapor permeable fabric ("breathable") to help reduce the risk of heat stress
- Optimized fit, improving wearer comfort and safety
- Low Linting

Material Diagram



Seam Diagram



Performance Standards



PARTIAL BODY
PROTECTION ONLY



TYPE PB [6]



0598



EN 14126

EN ISO 13688:2013

Product Information

Product Information	
Available Sizes	S, M, L, XL, 2XL
Color	White
Country Of Origin	China
Packaging Overview	Individually Packed
Product Material	Microporous polyethylene Laminate non-woven
Product Reference	2000 STANDARD Trousers - Model 301
Standards Overview	CE CATEGORY III (Type PB (6)-B, EN 14126)
Seam Type	Bound
Shelf Life	5 years

Suit components & accessories

Suit Components and Accessories	
Design Features	Elastication to waist and ankles, bound seams.

For additional information visit us at www.ansell.com, or call us at

Europe, Middle East & Africa Region
Ansell Healthcare Europe NV
T: +32 (0) 2 528 74 00

North America Region
Ansell Healthcare Products LLC
T: +1 800 800 0444

Australia
Ansell Limited
T: +61 1800 337 041

Asia Pacific Region
Ansell Global Trading Center
T: +603 8310 6688

Latin America & Caribbean Region
Ansell Commercial Mexico S.A. de C.V.
T: +52 442 248 1544 / 248 3133

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending: www.ansell.com/patentmarking © 2025 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.

