



Main

Range	Thorsman
Range of product	Thorsman Hand Light
Product or component type	Lighting
Light source	LED

Complementary

Type of installation	Outdoor
[Ue] rated operational voltage	3.7 V
Operational power in W	3 W
Battery type	1.5 Ah x lithium 3.7 V 3 h 8 h
Luminous flux	280 lm
Colour temperature	6000...7000 K
Material	Plastic
Product weight	155 g

Environment

IP degree of protection	IP20
IK degree of protection	IK07
Ambient air temperature for operation	-10...40 °C

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
Sustainable packaging	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.