

## **A-1200 ; 0...100 bar gauge; one switching output (PNP)**

### **A-1200 ; 0...100 bar gauge; one switching output (PNP)**

Item number: 46967537

Quantity: 1 pcs.

Order code: A-1200-D-BG510-1GI1-3K1HI-M4ZZS-ULZZ  
GSA5

W1011A12-ZZPSIOW-

Overview: A-1200 ; 0...100 bar gauge; one switching output (PNP)

Accuracy: 1.0% of span

Measuring range: 0...100 bar gauge

Process connection: G1/4 A ISO1179-2

Sealing: NBR

Permissible medium temperature: -30...+100°C

Output signal: one switching output (PNP)

IO-Link: IO-Link 1.1

Status Indication: Integrated indication

Power supply: 10 ... 32 V DC

Electrical connection: circular connector M12x1, 4-pin

pin assignment: U+=1, U-=3, SP1/C=4

Overload Safety: 2 x

Approvals: cULus

Test protocol: with test protocol

Type of packaging: single packaging

Specifications according to data sheet: PE 81.90

Details: A-1200 ; 0...100 bar gauge; one switching output (PNP)

Accuracy: 1.0% of span

Measuring range: 0...100 bar gauge

Process connection: G1/4 A ISO1179-2

Sealing: NBR

Permissible medium temperature: -30...+100°C

Output signal: one switching output (PNP)

IO-Link: IO-Link 1.1

Status Indication: Integrated indication

Power supply: 10 ... 32 V DC

Electrical connection: circular connector M12x1, 4-pin

pin assignment: U+=1, U-=3, SP1/C=4

Overload Safety: 2 x

Approvals: cULus

Test protocol: with test protocol

Type of packaging: single packaging

Specifications according to data sheet: PE 81.90