

Geberit ACO 203plus pressing tool [2], 230 V, in case



APPLICATION PURPOSES

- For pressing Geberit pressing systems

CHARACTERISTICS

- Geberit compatibility [2]
- LED pressing point light
- With Bluetooth® interface for the NovoCheck app
- Hydraulic
- Brushless motor
- Case can be equipped with Geberit set of pressing jaws [2]

TECHNICAL DATA

Nominal force	32 kN
Degree of protection	IP20
Nominal voltage	230 V AC
Operating voltage	18 V DC
Rechargeable battery type	lithium-ion battery
Operating temperature	-20 – +60 °C
Operating temperature, rechargeable battery	-10 – +50 °C
Sound pressure level	78 dB(A)
Sound power level max.	89 dB(A)
Vibration emission value max.	2.5 m/s²

SCOPE OF DELIVERY

- Battery-operated pressing tool [2], 18 V DC
- Battery charger
- Cleaning agents and lubricants
- 2 lithium-ion rechargeable batteries, 18 V / 5 Ah
- Case

ACCESSORIES

- Geberit carrying belt for case
- Geberit Li-ion battery 18 V

Art. no.	Compatibility	Protection class	Power consumption W	Plug type	Weight of main element kg
This article is suitable for the following system: Geberit Mepla					
691.219.P5.2	[2]	III	90	BS 1363 A	9.739

Art. no.	Compatibility	Protection class	Power consumption W	Plug type	Weight of main element kg
This article is suitable for the following system: Geberit Mapress					
691.219.P5.2	[2]	III	90	BS 1363 A	9.739