



Main

Range of product	Actassi
Product or component type	19" uprights
Device application	Overhead patching
Number of units 19" - Height	4U - 350 mm
Installation mode	Cable ladder mounted Tray mounted Overhead
Applications	To mount 19" equipment
Enclosure type	Open frame
Colour	Uprights: raven black

Complementary

Device composition	2 x 19" uprights
Load rating	15 kg static
Support equipment	2 x 19" uprights (vertical) 4 x mounting bracket (angled) 4 x bolts and nuts 4 x cord self-lock grip strip 2 x cord manager 1 x label holder
Material	Steel
Surface finish	Epoxy-polyester powder
Width	500 mm
Depth	160 mm

Environment

Standards	EIA-310D IEC 60297-3-100
-----------	-----------------------------

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations