

Specifications for Nylon Cloth tape for BMP21-PLUS; BMP21; IDPAL; LABPAL

Adhesive	Permanent Acrylic
Article No.	110938
Brady Material No.	B-499
Material Type	Nylon Cloth
Colour	Black on White
Finish	Matt
Order Reference	M21-375-499-TB
Printable Area - Height (mm)	4800.00
Printable Area - Width (mm)	9.53
Printer Compatibility	BMP21-PLUS; BMP21-LAB; BMP21; IDPAL; LABPAL
Size - Length (m)	4.90
Size - Width (mm)	9.53
Additional Information	High adhesion, Low profile
Thickness (mm)	0.166
Total Qty per Pack	1 Roll(s) / Box
Approval/Compliance	UL Recognised; CSA Accepted
Application	Communication Cabling; Panel Identification; Voice & Data Communication; Wire & Cable Marking
Continuous vs Die Cut Labels	Continuous Tape
Environment	Freezer; Liquid Nitrogen; Autoclave
Industry	Laboratory; Electrical; Healthcare; Buildings ID
Laboratory Application	Vial & Tube Labels; Plate; General Identification
Description	Nylon cloth tape.
Max. Service Temp. °C	90
Min. Service	-40

Temp. °C	
Surface	For smooth, textured/rough or Highly textured/Low surface energy surfaces
Voice/Data Application	Patch Panels