

# PRODUCT SPECIFICATION

<b>Brand</b>	C.K
<b>Product Range</b>	Crimping pliers
<b>Catalogue number</b>	3645, 3646 & 30024
<b>Date</b>	10/02/2012

<p><b>Range Description</b> Crimping pliers for cable links</p>				
<p><b>Features</b></p> <ul style="list-style-type: none"> <li>• High alloy carbon steel, drop forged – for long life</li> <li>• Matt chrome plated – for corrosion resistance</li> <li>• Contoured grips with anti-slip horns – for comfort and safety</li> </ul>				
<ul style="list-style-type: none"> <li>• Specially hardened steel for durability</li> <li>• Four function tool</li> <li>• Soft wire cutting only</li> <li>• Crimping of non-insulated terminals (1.5, 2.5 &amp; 4-6mm)</li> <li>• Crimping of insulated terminals (Red, Blue &amp; Yellow)</li> <li>• Bolt shearing (2.6, 3.0, 3.5, 4.0 &amp; 5.0mm Diameter)</li> <li>• Wire stripping (0.75, 1.0, 1.5, 2.5, 4.0 &amp; 6.0mm<sup>2</sup>)</li> <li>• Soft grips for prolonged comfortable use</li> </ul>				
Item Number	Item Description	EAN No	Commodity code	Carton Qty
430005	Crimping pliers for cable links on wire 0.25-2.5mm square, AWG 23-13	5051074300058	82032090	3
430006	Crimping pliers for cable links on wire 0.5-16mm square, AWG 20-5	5051074300065	82032090	3
430024	Muti function crimping tool	5051074300249	82032090	

Technical product information	
Standards compliance	None applicable
User health and safety information	None applicable
RoHS/WEEE compliance	This product range does not fall within the scope of RoHS or WEEE regulations
Material safety data	None applicable
Warranty	C.K tools are guaranteed for life against imperfect materials or workmanship
Country of origin	43005 & 6 – Germany 430024 - Taiwan

### Dimensional details

Item	Product only				Product on primary packaging			
	Width mm	Depth mm	Height mm	Net weight g	Width mm	Depth mm	Height mm	Gross weight g
430005	56	17	150	166	60	25	220	180
430006	58	12	230	256	60	25	260	271
430024	62	13	230	224	92	20	300	258

Item	Shelf box (secondary packaging)				Euro Pallet data Wi x Hi	
	Width mm	Depth mm	Height mm	Gross weight g	No of cartons on base	Number of rows high
430005	85	250	60	603		
430006	90	290	60	892		
430024						

### Packaging waste details

Item	Primary Packaging				Secondary packaging			
	Plastic g	Use	Card g	Use	Plastic g	Use	Card g	Use
430005	15	Hanger					63	Box
430006	15	Hanger					79	Box

430024								
--------	--	--	--	--	--	--	--	--