

18V Impact Wrench LXT®

DTW1005

3/4", 1 360 Nm, 0 – 1 800 min⁻¹

Model DTW1005 is an Impact Wrench, High power, equipped with a long anvil and powered by a 18V LXT Li-Ion battery.

Main feature and benefits:•Tip shape: Long anvil with 19mm (3/4") Square drive•Style of socket retention: C ring (with a hole)•Electronic 4-stage impact power selection•Constant speed control



Technical specifications

Nominal Battery Voltage	18 V
Voltage LXT	✓
Max Fastening Torque Impact Drill	50 / 150 / 450 / 1360 Nm
No load speed	0 - 800 / 900 / 1000 / 1800 min ⁻¹
Impacts per Minute (IPM)	0 - 1600 / 1800 / 2200 min ⁻¹
Drive Square	3/4 "
Tightening Capacity Standard Bolt	M12 - M33
Tightening Capacity High Tensile Bolt	M10 - M24
Sound Power Level (L _{WA})	108 dB(A)
Sound Pressure Level (L _{pA})	100 dB(A)
Noise Uncertainty (K Factor)	3 dB(A)
Tool weight with battery	3,9 - 4,2 kg
Product Dimensions (L x W x H):	339 x 91 x 291 mm

User benefits

- Brushless maintenance-free and long-life motor
- Ergonomic soft grip handle provides increased comfort
- LED light illuminates the work site
- Electronic 4 stage impact power selection for added versatility
- Electric brake for maximum productivity and increased operator safety
- Reverse rotation Auto Stop mode stops after the bolt/ nut loosened enough
- Wide hanging hook, e.g. for scaffolding
- Battery protection system automatically shuts off power when the battery level is low

Link to product - www.makitauk.com



Related products

Other

User manual

Parts drawing