

Product specifications **142VP**

Last update: 6/18/10 12:38:07 PM

**General**

Description	Dunlop Protomastor full safety
Upper/Sole Color	Green/Black
Status	Stock,
Segment	Agriculture
Product line	Functional
Sizerange/#	36-48/13
Hangtag	
Insole	
Lining	White polyester
Resistance code	2

**Safety**

Standard	EN345.S5
	<input checked="" type="checkbox"/> Steel Toecap <input checked="" type="checkbox"/> Antistatic
	<input checked="" type="checkbox"/> Steel Midsole <input checked="" type="checkbox"/> Energy absorbing
	<input checked="" type="checkbox"/> Oilresistant sole <input type="checkbox"/> Cold insulating
Safety marking	
Manual	Dunlop EN manual

Sole info

Sizing	<input checked="" type="checkbox"/> French <input checked="" type="checkbox"/> English <input type="checkbox"/> U.S.
Date of manufacturing	<input checked="" type="checkbox"/>
Other sole info	Planeta Plasticos Made in Portugal

Labeling/marking

Marking	Dunlop stamp
Barcode on boot	Barcode label
Barcode packaging	Dunlop label
Barcode outercarton	Dunlop label

Remark

Weight 43: 2,39 kg/pr

Packaging		Sealed milky polybag						
Size	Boxtype	Length	Width	Height	Pairs/Box	Boxes/layer	#Layers	Pallet height
38-42	PT2	390	390	360	6	6	5	1.95
43-48	PT3	390	390	395	6	6	4	1.75
36-37	PT1	390	390	273	6	6	6	1.83