

Flange - PTFIX 10/S-F - 1082917


Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Flange, with screw-on fixing, length: 37 mm, width: 8.6 mm, height: 25.1 mm, color: gray



Key Commercial Data

Packing unit	20 pc
Minimum order quantity	20 pc
GTIN	 4 055626 817033
GTIN	4055626817033
Weight per Piece (excluding packing)	4.250 g
Custom tariff number	85389099
Country of origin	Poland
Sales Key	BE2ZWX

Technical data

General

Color	gray
Material	PA
Ambient temperature (operation)	-60 °C ... 105 °C (max. short-term operating temperature 130°C)
Ambient temperature (storage/transport)	-25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C)
Permissible humidity (storage/transport)	30 % ... 70 %
Ambient temperature (assembly)	-5 °C ... 70 °C
Ambient temperature (actuation)	-5 °C ... 70 °C

Dimensions

Width	8.6 mm
Length	37 mm
Height	25.1 mm

Flange - PTFIX 10/S-F - 1082917

Classifications

eCl@ss

eCl@ss 10.0.1	27141190
eCl@ss 11.0	27141190
eCl@ss 8.0	27370419
eCl@ss 9.0	27370419

ETIM

ETIM 5.0	EC001024
----------	----------

Approvals

Approvals

Approvals

EAC

Ex Approvals

Approval details

EAC		RU C- DE.AI30.B.01102
-----	---	--------------------------
