

# RAMSES 706 S


Item no.: 7060003

theben

Climate control  
Room thermostats

## Description

- Electronic room thermostats for all types of heating, e.g. gas, water, electric heating etc.
- Snap function, easy installation without screws
- Temperature control via control wheel
- Switch for on/off + indicator light
- Dimmable and switchable LEDs
- Rings under the adjustment wheel to limit the target temperature
- Temperature setting range 5 ... 30°C
- External temperature reduction possible via control with time switch




## Technical data

RAMSES 706 S	
Operating voltage	230 V AC
Frequency	50 - 60 Hz
Type of contact	NC contact
Switching output	Not potential-free
Switching capacity	10 A (at 230 V AC, $\cos \varphi = 1$ )
Setting range temperature	5°C ... 30°C
Function	Electronic

RAMSES 706 S	
Hysteresis	-
Control accuracy	$\pm 0.25$ K
Colour	White (similar RAL 9010)
Installation type	Surface-mounted
Type of protection	IP 40
Protection class	II according to EN 60 730-1

## Connection example



Subject to technical changes and misprints

additional information at: [www.theben.de/product/7060003](http://www.theben.de/product/7060003)


The load data are determined with exemplary selected illuminants and are therefore typical data due to the large number of available products.

# RAMSES 706 S

Item no.: 7060003

**theben**

## Scale drawings



## Accessories

**Adapter plate RAMSES 714**  
Item no.: 9070212

**Actuator ALPHA 5 230 V**  
Item no.: 9070441



Subject to technical changes and misprints

additional information at: [www.theben.de/product/7060003](http://www.theben.de/product/7060003)

The load data are determined with exemplary selected illuminants and are therefore typical data due to the large number of available products.