

Datasheet

Stock No: 415-6242

RS Pro Cast Iron 152 Base Flange, 48.3mm Round Tube, Type 3



Product Details

Base Flange

Upright pivots up to 11° from vertical

Dimensions (mm)						
Tube Size Ref.	B	C	D	E	F	G
3	96	10	152	14	90	114

Note

The 'selection guide' table links the alphabetical key in the illustration to the specific fittings (a typical stock number is also quoted).

Specifications

Structural Element Type	Round Tube
Connector Type	Joint
Fits Strut Profile	Type 3
Fits Tube Diameter	48.3mm
Product Family	RS Handrail System
Material	Cast Iron
Product System	150

Gradient Fittings

The line drawing illustrates some typical applications of the gradient fittings for the construction of handrails on slopes and ramps between 0° - 11°.

For tube Size Ref. 3 (48.3mm OD tube)

The 'selection guide' table links the alphabetical key in the illustration to the specific fittings (a typical stock number is also quoted).

Selection Guide		
Key	Fitting Description	Typical Stock No.
SA	Base flange	415-6242
SB	Short Tee	415-6258
SC	Elbow	415-6270
SD	Long Tee	415-6286
SE	Two Socket Cross	415-6292

Specifications

Component Type	Base Flange
Structural Element Type	Round Tube
Product Family	RS Handrail System
Product System	152
Fits Round Tube Size	Type 3
Fits Tube Diameter	48.3mm
Fits Strut Profile	Type 3
Material	Cast Iron