

## FEATURES

- **Grey Colour:** Blends seamlessly with industrial settings
- **AC Current Type:** Compatible with standard AC power supplies
- **ABS Housing:** Provides durability and resistance to impact
- **IP43 Rating:** Offers protection against solid objects and water spray
- **Maximum Operating Temperature of 50 °C:** Suitable for a wide range of environments
- **Maximum Sound Level of 88 dB:** Ensures clear audible alerts
- **Wall Mount Type:** Easy installation on walls
- **Single Tone Type:** Provides a consistent and steady sound

## RS PRO Grey AC Horn, ABS Housing

RS Stock No: 658-307



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

### Product Description

The RS PRO Grey AC Horn is designed for effective audible signalling in industrial environments. With a robust ABS housing, it is suitable for wall mounting and delivers a steady tone to alert personnel. Ideal for use in areas where clear sound notification is essential, this horn operates at a maximum supply voltage of 230 V AC.

### General Specifications

Colour	Grey
Mount Type	Wall
Number of Tones	1
Product Type	Horn
Tone Type	Steady

### Electrical Specifications

Current Type	AC
Maximum Supply Voltage	230 V ac

### Mechanical Specifications

Housing Material	ABS
------------------	-----

### Protection Category

IP Rating	IP43
-----------	------

### Operation Environment Specifications

Maximum Operating Temperature	50 °C
-------------------------------	-------

### Measurement Specifications

Maximum Sound Level	88 dB
---------------------	-------

### Approvals

Standards/Approvals	CE, EAC
---------------------	---------