



## DSCP-25 0240

E1441383

Branch Connector 2-Pole, 5-Conductors/Pole, 0.2-4.0mm<sup>2</sup>



### Product Properties:

Number of clamp positions (device side)	10 .
Type of locking/unlocking	Lever
Nominal voltage	450 V
Nominal current	32 A
Suitable for solid conductors	Yes
Transparent	Yes
Number of clamp positions	10 .
With operation lever	Yes
Suitable for solid core	Yes
Suitable for flexible core	Yes
Suitable for multi-wire core	Yes
Strip length	12 mm
Colour	Multi-coloured
Operating temperature	-40-105 °C
Flammability rating (UL94)	V2

### Dimensions:

Max. AWG-size	12
Min. AWG-size	Other
Nominal cross section (device side)	0.2-4 mm <sup>2</sup>
Nominal cross section (installation side)	0.2-4 mm <sup>2</sup>
Cable diameter	1-4 mm

Conductor cross section flexible (fine-strand) with cable end sleeve	0.2-4 mm <sup>2</sup>
Conductor cross section solid (solid, stranded)	0.5-4 mm <sup>2</sup>
Width	21 mm
Height	18 mm
Strip length	12 mm
MOQ	20 .
Unit	pcs
Nominal cross section	0.2-4 mm <sup>2</sup>
Length	30 mm
Nominal voltage	450 V

### **Approvals:**

Approved according to CE	Yes
Approved according to TUV	Yes
Approved according to UKCA	Ja

### **Compliance:**

REACH	No SVHC (Latest. 04 Feb 2026)
RoHS	RoHS 3 (2015/863)
SCIP	Not Applicable
US TSCA	No (5 PBT Subs, Feb 2021)

### **Other information:**

ETIM-Class	EC000446 - Screwless terminal
ETIM-Release	9.0
Trademark	NEMIQ
Product Group	102016
Search Description	ENR2026V, SKV2026MK
Alternative SKU	DSCP-250240
E-no	E1441383

### **Logistic information:**

Barcode	733117642980
Country of origin	CN
E-no	E1441383
Item status	Stock item, normally in stock with reservation for in between sales.
MOQ	20 .
Stock code	DSCP-25 0240
Taric code	85369010
Unit	pcs

