

FEATURES

- **Sintered Bronze Material:** Provides excellent wear resistance and longevity.
- **Flanged Design:** Ensures secure positioning and easy installation.
- **Dynamic Load Rating of 14 N/mm²:** Suitable for applications with varying loads.
- **Static Load Rating of 50 N/mm²:** Capable of handling high static loads.
- **Bore Size of 16.02 mm:** Compatible with a wide range of shafts.
- **Outside Diameter of 20.05 mm:** Fits standard housing dimensions.

RS PRO 16.02 mm Flanged Plain Bearing

RS Stock No: 529-039



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

This RS PRO flanged plain bearing is designed for applications requiring reliable performance under varying load conditions. Made from high-quality sintered bronze, it offers excellent durability and resistance to wear. Ideal for use in machinery where low maintenance and high efficiency are crucial.

General Specifications

Bore Size	16.02 mm
Dynamic Load Rating	14 N/mm ²
Product Type	Plain Bearing
Static Load Rating	50 N/mm ²
Sub Type	Flanged

Mechanical Specifications

Material	Sintered Bronze
Outside Diameter	20.05 mm
Width	20 mm

Approvals

Standards/Approvals	ISO 2795, ISO 9001:2008, UKAS 001
---------------------	-----------------------------------